


# E40632



## Welding adapters EN10357 series D (SMS)

ADAPT EN10357-D DN40



Application	
Design	for volumetric flow meters SMF
Application	food and beverage industry; hygienic systems
Pressure rating	40 bar / 4 MPa
Tests / approvals	
Pressure Equipment Directive	A possible classification to PED depends on the application and has to be carried out by the user / operator.
Safety instructions	The compatibility between medium and product material has to be checked in all applications.
Mechanical data	
Weight [g]	2361.7
Materials	stainless steel (316L/1.4404)
Nominal diameter	DN40 (1 1/2")

# E40632



## Welding adapters EN10357 series D (SMS)

ADAPT EN10357-D DN40

Sensor connection	ifm-specific device flange
Process connection	welding adapter EN10357 series D (SMS); ISO 2037
Process connection suitable for pipe standard	(DIN EN 10357 Series D); (ISO 2037)
Surface characteristics Ra/Rz of the wetted parts	$Ra \leq 0.4 \mu m$
<b>Accessories</b>	
Items supplied	screws 8
<b>Remarks</b>	
Pack quantity	2 pcs.