



Product: [8760ELW](#)

Electronic, 2 C #18 Str TC, PE Ins, OS, LSZH Jkt, Cca

[Request Sample](#)

Product Description
Electronic, 2 Conductor 18AWG (16x30) Tinned Copper, PO Insulation, Overall Beldfoil® Shield, LSZH Outer Jacket, CPR Cca

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Pairs
18	16x30	TC - Tinned Copper	1
Conductor Count:			2

Insulation		
Material	Nominal Diameter	Diameter +/- Tolerance
PE - Polyethylene	2.08 mm	0.05 mm

Color Chart	
Number	Color
Pair 1	Black & Clear

Outer Shield						
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	20	7x28

Outer Jacket			
Material	Color	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	Chrome (RAL 7037)	6.0 mm	0.89 mm

Electrical Characteristics

Conductor DCR	
Nominal Conductor DCR	
21.3 Ohm/km	

Capacitance	
Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
98 pF/m	144 pF/m

Inductance	
Nominal Inductance	
0.591 µH/m	

Current	
Element	Max. Recommended Current [A]

Conductor(s)	5.2 Amps per Conductor at 25°C
--------------	--------------------------------

Voltage

Voltage Rating [V]
300 V

Temperature Range

Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Max. Pull Tension:	280 N
Min. Bend Radius/Minor Axis:	60 mm

Standards

CPR Euroclass:	Cca-s1,d1,a1
CENELEC Compliance:	EN 50290-2-20

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Cca
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU CE Mark:	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	60%

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #
8760ELW.00500
8760ELW.01500

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.45 Revision Date: 02-03-2025
----------------------	---

© 2025 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and

regulations based on their individual usage of the product.