

M18 FHIW2F12

M18 FUEL 1/2" HIGH TORQUE IMPACT WRENCH



- More Compact, greater access in Tight spaces with only 193mm in overall length.
- Light in weight at only 2.68kg, best-in-class solution.
- 1/2" drive, producing up to 2,169Nm of maximum torque for the toughest applications.
- Battery Isolation system provides secure connection and controls vibration transmitted to the pack
- Strengthened Anvil material enables tool to reliably produce the maximum performance
- M18 Forge 6.0Ah Battery delivers longer runtime and more power

Battery System	M18
Max. Nut-busting Torque	2,169 Nm
No-Load Speed	0 – 700 / 1,300 / 2,000 / FWD:0 - 900, REV: 2,000 – 750 RPM
Impact Rate	0 -1,300 / 2,200 / 2,400 / 2,400 IPM
Fastening Torque	880 / 1,220 / 1,627Nm
Max. Bolt Diameter	M36
Anvil	1/2" Square w/ Friction Ring
Weight (Tool-Only)	2.68 kg
Recommended Battery	M18 Forge 6.0Ah, M18 5.0 Ah