



Datasheet RS PRO Piezo Audio Transducer EN

RS Stock No: 181-2724



A.SCOPE


This specification applies piezo audio transducer, 1812651

B. SPECIFI	CATION
------------	--------

No.	ltem	Unit	Specification	Condition
1	Operating Volt. MAX	Vp-p	MAX 50	
2	Current consumption	mA	MAX 10	at 10Vp-p,square wave,800Hz.
3	Sound pressure level	dB	MIN 80	at 10cm/10Vp-p,square wave,800Hz
4	Electrostatic capacity	pF	70,000 ± 30%	at 120Hz/1V
5	Operating temp.	°C	-30 ~ +80	
6	Storage temp.	°C	-40 ~ +80	
7	Dimension	mm	ϕ 60.8 x H14.0	See appearance drawing
8	Weight (MAX)	gram	12.0	
9	Material		PA-777D (BLACK)	
10	Terminal		Wire type	See appearance drawing
11	Environmental Protection Regulation		RoHS	








Tol: ± 0.5 Unit: mm


D. TYPICAL FREQUENCY RESPONSE CURVE E. MEASURING METHOD



S.P.L. Measuring Circuit Input Signal: 10Vp-p,800Hz, Square Wave







Mic : RION S.P.L meter UC30 or equivalent

S.G : Hewlett Packard 33120A Function Generator or equivalent

F. MECHANICAL CHARACTERISTICS

No.	ltem	Test Condition	Evaluation standard
1	Solderability (Connector excepted)	ISINDOED WIRES OF 1840 WIRES ARE IMMERSED IN TOSIN TOP 3	
2	Lead Wire Pull Strength	The pull force shall be applied to double lead wire : Horizontal 3.0N(0.306kg) for 30 seconds. Vertical 2.0N(0.204kg) for 30 seconds.	No damage and cutting off.
3	Vibration		I he value of oscillation frequency/ current consumption should be in +10% compared with initial
4	Drop test	The part only shall be dropped from a height of 75cm onto a 40mm thick wooden board 3 times in 3 axes (X.Y.Z). (a total of 9 times).	





G. ENVIRONMENT TEST

No.	ltem	Test Condition	Evaluation standard
1	High temp. test	After being placed in a chamber at +80 $^\circ\!\mathrm{C}$ for 240 hours	
2	Low temp. test	After being placed in a chamber at –40 $^\circ\!{ m C}$ for 240 hours	
3	Humidity test	After being placed in a chamber at +40 $^\circ\!C$ and 90±5% relative humidity for 240 hours	
4	Temp. cycle test	+80°C +25°C +25°C	Being placed for 4 hours at +25°C, buzzer shall be measured. The value of oscillation frequency/ current consumption should be in±10% compared with initial ones .The SPL should be in±10dB compared with initial one.

H. RELIABILITY TEST

No.	ltem	Test condition	Evaluation standard
1	Operating life test	 Continuous life test 48 hours continuous operation at +65°C with rated voltage applied. Intermittent life test A duty cycle of 1 minute on, 1 minutes off, a minimum of 5000 times at room temp.(+25±2°C) and rated voltage applied. 	Being placed for 4 hours at $+25^{\circ}$, buzzer shall be measured. The value of oscillation frequency/ current consumption should be in $\pm 10\%$ compared with initial ones .The SPL should be in ± 10 dB compared with initial one.

TEST CONDITION.

Standard Test Condition:a) Temperature : $+5 \sim +35^{\circ}$ Cb) Humidity : 45-85%c) Pressure : 860-1060mbarJudgement Test Condition:a) Temperature : $+25 \pm 2^{\circ}$ Cb) Humidity : 60-70%c) Pressure : 860-1060mbar



