

## Features

- High temperature
- High Capacity

## RS PRO Rechargeable Battery Lithium-ion 14.40V

RS Stock No.: 0683438




RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

The RS PRO Rechargeable Lithium Ion Cylindrical Battery has a long service life, up to 1000 charge/discharge cycles. This product provides a reliable and safe power source with a wide range of temperature reliability, low discharge rate and great overcharge.

## General Specifications

Battery type	Lithium ion 18650 battery pack (4S2P)
Nominal voltage	14.4V
Nominal capacity	7000 mAh ( at 0.2C CC to 2.5V)
Minimum capacity	6800 mAh ( at 0.2C CC to 2.5V)
Standard discharge current	0.2C ( 1400mA) Constant current end condition (cut off)
Maximum Discharge current	≤3A ( ambient temperature 25°C) Continuous output discharging current 3A)
Discharge cut off voltage	10.8V±0.08V
Maximum Charge voltage	17V±0.08V (CC-CV to 17V, 50mA cut off)
Maximum Charge Current	1750 mA (CC-CV to 17V, 50mA cut off)
Weight	Approximate: 365g
Dimension	73x68x42±(1-2-2mm)



1.	Positive	Red one wire with 22AWG	Length: $120 \pm 10 \text{ mm}$
2.	Negative	Black one wire with 22AWG	Length: $120 \pm 10 \text{ mm}$

## Approvals

Declarations	MFR Declaration of Conformity
Hazardous Area Certification	ATEX / IECEx
Standards Met	VDE

## Battery Pack Specifications

Item		Parameters	
Nominal Voltage		14.40V	
Typical capacity		7Ah ( At 0.2C, CC to 2.5V)	
Minimum capacity		6.8Ah	
Discharge	Standard discharge current	0.2C (1400mA) Constant current end condition (cut off)	
	Maximum Discharge Current	≤3A (ambient temperature 25°C) Continuous output discharging current 3A)	
	Cut -off voltage	10.8V±0.08V	
Charge	Maximum Voltage	17V±0.025V	
	Maximum Current	1750mA	
	Charge mode	CC-CV to 17V,50mA cut off	
	Discharging Inner resistance	≤ 100mΩ AC1kHz	
Operation temperature / humidity range	Discharge	-20□ ~ +50□	
		When the environment temperature is higher than 45□, please pay attention to ventilation and heat rejection.	
Storage temperature/ humidity range	One month	-20□ ~ +50□	Recovery ratio≥80%
	Three months	-20□ ~ +45□	Recovery ratio≥80%
	One year	20□ ~ +25□	Recovery ratio≥80%
Protection function	Over charge protection, over discharge protection		
Shell material	PVC		
Weight	365g		
Size ( L* W*H) mm	73 x68x42± (1-2-2mm)		

## Protective circuits (CL-S04-019-A01-M4ST)

Item	Min	Typ	Max	Unit
Over-Charge protection voltage	4.225	4.25	4.275	V
Over-Charge Release voltage	4.10	4.15	4.20	V
Over-Discharge protection Voltage	2.62	2.70	2.78	V

Over-Discharge Release Voltage	2.90	3.00	3.10	V
Overcurrent discharge protection	13A±4A			
Overcurrent discharge protection delay	10±5ms			
Method of over discharge protection release	Charge activate			
Over-Current Discharge Protection Release	Release load			
Short circuit current protection	Enable			
Short circuit current protection delay	200uS~800uS			
Short circuit protection release	Release Load			
Idle mode	≤50 uA			
Short circuit current protection	Enable			
Maximum continuous discharge current	4A			
Main loop electrify resistance	≤100mΩ			
The size of final PCM	L38±0.5mm; W16±0.5mm; H<0.8			

## Cell information



### 1. Basic Characteristics

Technical Parameters	Specification		Condition/Note
3.1 Capacity	Typical	3500 mAh	Standard charge/discharge (Refer to 4.1 and 4.2)
	Minimum	3400 mAh	
3.2 Nominal Voltage	3.6V		

3.3 Internal Impedance	≤60mΩ	AC 1kHz	
3.4 Standard Charge (Refer to 4.1)	0.3C(1020mA) 4.2V 50mA	Constant current Constant voltage End condition (Cut off)	
3.5 Max. Charge Voltage	4.20V		
3.6 Rapid Charge Current	0.5C (1700mA)		
3.7 Standard Discharge	0.2C(680mA) 2.5V	Constant current End condition (Cut off)	
3.8 Max. Discharge Current	0.5C (1700mA) 1.5C(5100mA)	-20~5°C 5~50°C	
3.9 Max Pulse Discharge Current	2.0C (6800 mA)		
3.10 Operating Temperature (Charge)	0~45°C		
3.11 Operating Temperature (Discharge)	-20°C~50°C		
3.12 Storage Temperature (for Shipping State)	One month	-20°C~50°C	Recovery ratio≥80%
	Three months	-20°C~45°C	Recovery ratio≥80%
	One year	-20°C~25°C	Recovery ratio≥75%
3.13 Weight	Max. 49.0g		
3.14 Max. Dimension	Diameter(Φ)	18.6mm	
	Height(H)	65.2mm	

## 2. Standard Conditions for Test

- Without stating specifically, all the electrical characteristics are obtained under the following conditions: Ambient temperature: 25±2°C; Relative humidity: ≤75%.
- Without stating specifically, all the safety tests are conducted under the following conditions:

Ambient temperature :25±2°C; Relative humidity: ≤75%.

4.1 Standard Charge	0.3C (1020mA), CC-CV to 4.2V, 50mA cut off
4.2 Standard Discharge	0.2C(680mA), CC to 2.5V
4.3 Charge/Discharge Condition	Charge:0.3C(1020mA), CC-CV to 4.2V, 50 mA cut off, rest for 10min. Discharge: 0.5C(1700mA), CC to 2.5V, rest for 20 min.

### 3. Characteristics Electrical Characteristics

Items	Test Procedure	Requirements	
5.1.1 Nominal Voltage	Charge as described in 4.1, and discharge as described in 4.2. Calculate the average working voltage during discharge process.	3.6V	
5.1.2 Discharge Characteristic	Charge under the condition of 4.1, and discharge under the condition of 4.2.	≥3400mAh	
5.1.3 Cycle Life	Charge as described in 4.1, rest for 10min, and discharge with the current of 0.5C(1625mA) to 2.75V and then rest for 20min. Repeat cycling till discharge capacity in 2 successive cycle is less than 80% of the initial capacity.	≥300 Cycles	
5.1.4 Rate Performance	Charge as described in 4.1, rest for 10min, and discharge with different constant current and cut off at 2.5V. Calculate the ratio of above capacities to the standard discharge capacity as described in 4.2.	0.2C	=100%
		0.5C	≥94%
		1C	≥90%
		2C	≥80%
5.1.5 Storage at High Temperature	Charge as described in 4.1, store in the environment with temperature of 60±2°C for 7 days, and discharge as described in 4.2: charge and discharge as described in 4.3 for 3 times and record the recovery capacity.	Recovery ratio ≥80%	
5.1.6 Temperature Dependency of Capacity	Charge as describe in 4.1, and discharge in the environment with different temperatures. Calculate the ratio of above discharge capacities to discharge capacity at temperature of 25±2°C.	-10°C	≥70%
		0°C	≥80%
		25°C	=100%
		50°C	≥95%
5.1.7 Capacity Retention at Room Temperature	Fully charge as described in 4.1, store for 30days, and discharge as described in 4.2. Calculate the retention ratio of capacity.	Retention ratio ≥90%	
5.1.8 Storage	(After Manufactured within 3 months) Charge as described in 4.1 until the capacity reaches 40-50%; store for 12 months in the environment with relative humidity of 45%~85%; charge and discharge as described in 4.1 and 4.2, respectively, and record the discharge capacity and calculate the retention ratio of capacity.	Retention ratio ≥80%	

### Electrical Tests

Items	Test Procedures	Requirements
5.2.1 Short circuit at 20±5°C	The samples cell should be fully charged as described in 4.1 rest for 30min, and then short-circuited by connecting positive and	No fire, no explosion, and maximum

	negative terminals with a circuit load having a resistance of $80 \pm 20 \text{m}\Omega$ at $20 \pm 5^\circ\text{C}$ . The temperature of the case should be measured during the test. The cell should remain on test for 24 hours or until the temperature of the case declines by 20% of the maximum temperature.	surface temperature $\leq 150^\circ\text{C}$
5.2.2 Abnormal Charge	The sample cell should be discharged as described in 4.2, and subjected to the charging process to 4.6V with the current of the greater one between the 3C and three times of the charging current recommended by the manufacturer. The temperature of the case should be measured during the test. The test should be continued until the charging time reaches 7 hours or temperature of the case declines by 20% of the maximum temperature.	No fire, no explosion.
5.2.3 Forced-Discharge	The samples cell should be discharged as described in 4.2, and subjected to the forced discharge process with the reverse current of 1C. the test time is 90 min.	No fire, no explosion.

## Mechanical Tests


Items	Test Procedure	Requirements
5.3.1 Vibration	The samples cell should be fully charged as described in 4.1, and fixed on a vibration platform. Then it is to be subjected to simple harmonic motion with an amplitude of 0.8mm (1.6mm total maximum excursion). The frequency is to be varied at the rate of 1Hz/min between 10 and 55 Hz, and return in not less than 90 nor more than 100 min. The above process should be conducted at both axial and radical directions (three mutually perpendicular directions for prismatic and pouch cell).	No fire, no explosion, and no leakage.
5.3.2 Drop	The samples cell should be fully charged as described in 4.1, and dropped onto a flat concrete floor from 1m height. The positive and negative electrode side should be dropped once, respectively, and the cylindrical surface twice. Each cell should be dropped four times.	No fire, no explosion.
5.3.3 Impact	The sample cell should be fully charged as described in 4.1, and placed on flat surface. A metal bar with a diameter of 15.8mm(5/8 in) is to be placed across the center of the sample, and perpendicular to the longitudinal axis of the cell. A weight of 9.1kg(20 lb) is to be dropped from a height of 0.61m(24in) onto the sample.	No fire, no explosion.

5.3.4 Crush	The sample cell should be fully charged as described in 4.1, placed between two flat surfaces and crushed with its longitudinal axis parallel to the fat surfaces. Crush the cell in the direction perpendicular to the flat surface with a crushing force of $13.0 \pm 0.2 \text{ kN}$ . The test is completed once the crushing force reaches the maximum value.	No fire, no explosion.
-------------	--	------------------------

### Environmental Tests

Items	Test Procedure	Requirements
5.4.1 Low Pressure	The samples cell should be fully charged as described in 4.1, and stored for 6 hours at an absolute pressure of $11.6 \text{ kPa}$ ( $1.68 \text{ psi}$ ) and a temperature of $20 \pm 5^\circ \text{C}$ , followed by 1 hour's observation.	No fire, no explosion, and no leakage.
5.4.2 Heating	The sample cell should be fully charged as described in 4.1, and placed in a gravity or circulating air convection oven with an initial temperature of $20 \pm 5^\circ \text{C}$ . Raise the oven temperature at a rate of $5 \pm 2^\circ \text{C/min}$ to the test temperature $130 \pm 2^\circ \text{C}$ and remain at this temperature for 30 minutes.	No fire, no explosion.

### Outline Dimensions:



Unit: mm

Fig.1 Outline Dimensions of ICR18650-3500 mAh (with Tube)

## Cautions

Please read this specification carefully before testing or using the cells because improper handling of the Li-ion cells may lead to efficiency loss. Heating, electrolyte leakage, ignition or even explosion.

## Caution in Use

- Abnormal operations such as overcharge (voltage > 4.2V), over discharge (voltage < 2.5V) and overcurrent charge-discharge (maximum current allowed at present temperature) should be prohibited during cell using. It is strictly prohibited to use the cell in the environment easily causing problems, such as static electricity and poor sealing (water and dust entering).
- Charging with the current more than 0.5C(1625mA), using in the high-temperature/low-temperature, vibration, or humid environment, and matching unstable cells will reduce the cycle life of the cell.
- The cell shall not be used in the environment of high frequency microwave or ultrasonic wave. When using in series and parallel, it is recommended to coat the high -voltage wire with electromagnetic insulation cover to prevent the electromagnetic wave from damaging adjacent devices and human body.
- Avoid overlapping or contact between the positive and negative terminal wires of the battery to reduce the risk of short circuit.
- The battery should be charged and discharged in strict accordance with this specification to ensure the battery's cycle life and safety.
- When the batteries are assembled in a module for use. The cells with the same capacity, internal resistance, batch and charged state shall be used. The packing standard of the batteries should be strictly in accordance with the technical agreement, The temperature difference inside the battery pack should be less than 5°C when the pack is working.
- Do not charge the battery when temperature is less than 0°C, Please store it in the environment with temperature more than 0°C for a period before charging. Recommended store time as follows:

Outside Temperature	$-5^{\circ}\text{C} \leq T \leq 0^{\circ}\text{C}$	$-10^{\circ}\text{C} \leq T \leq -5^{\circ}\text{C}$	$-15^{\circ}\text{C} \leq T \leq -10^{\circ}\text{C}$	$-20^{\circ}\text{C} \leq T \leq -15^{\circ}\text{C}$
Time	2h	5h	8h	10h

## Safety Caution

- The battery should be placed away from babies and children. If there is any emergency such as deglutition, scald or explosion, please go to the hospital immediately.
- When charging or discharging the battery, please use professional test equipment designed for Li-ion batteries. Do not use ordinary constant current or constant voltage (CC/CV) power chargers without limitation of current or voltage. These chargers do not protect the battery from being overcharged and over-discharged, and may lead to function failure and be dangerous.
- When charging, discharging, or assembling the battery, avoid reversing the positive and negative terminals. Or it would lead to overcharge and over-discharge of the battery, causing serious failure, or even explosion.
- Do not solder the battery directly. Do not disassemble the battery.
- Do not put the battery in pockets or bags with metal objects, such as necklaces, hairpins, coins, screws, etc. Neither store the battery without proper isolation, nor connect the positive and negative electrodes directly with conductive materials. Or the battery may be short-circuited.
- Do not hammer, throw, or trample the battery. Do not put the battery into washing machines or high-pressure containers.
- Keep the battery away from heat sources, such as fires, heaters, etc. Do not use or store the battery in direct sunlight or at places where temperature could exceed 60°C. Or the battery may generate excessive heat. Ignite and fail.
- Do not get battery wet or throw it into water. When the battery is not in use, place it in a dry environment with relatively low temperature.
- If the battery becomes abnormally hot, give out a smell, change colour, deforms or show any other abnormalities during using, testing or storing, please stop using or testing immediately. Attempt to isolate the battery and stay away.
- If the leaking electrolyte from the battery gets into your eyes, do not rub your eyes. Rinse the eyes with clean and seek medical attention if problem remain. If the electrolyte gets onto the skin or clothing, wash clean water immediately.

## Packing

Cells need to be at half-charged state when packed. The surface of the packing boxes shall contain the following information: product name, type, nominal voltage, quantity, gross weight, date, capacity, and impedance.

## Long-term Storage

When delivered, cells are charged to the voltage of 3.2V~4.00V, storing cells at/more than 80% SOC for a long time will lead to capacity loss and cycle life loss. Please keep cells into use within 90 days when the capacity is more than 80%.

Cells may have lower capacity than they're expected due to the self-discharge when cells are to be delivered at 30% SOC.

Do not use or store the cells when the voltage is less than 2.5V