



Technical Data Sheet

3M™ Double Coated Removable Foam Tape 4658F

Product Description

3M™ Double Coated Removable Foam Tape 4658F is a clear, double coated acrylic foam tape that removes cleanly from many surfaces. 3M™ Adhesive 100 is a firm acrylic adhesive system that offers high ultimate bond strength, good temperature resistance, solvent resistance and static shear holding power. 3M tape 4658F can reach high bond strengths and some high surface energy substrates and may become difficult to remove.

Technical Information Note

The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

Typical Physical Properties

Attribute Name	Value
Color	Clear
Adhesive Type	100
Foam Density	960 kg/m ³
Foam Type	Acrylic

Attribute Name	Value
Thickness: Nominal	0.8 mm
Liner	Polyester Film
Liner Thickness	0.08 mm
Primary Liner Color	Clear
Thickness Tolerance	± 10 %

Typical Performance Characteristics

Substrate: Stainless Steel
Temperature: 23 °C
Dwell Time: 72 h
Backing: 5 mil Aluminum Foil

Attribute Name	Test Method	Value
90° Peel Adhesion	ASTM D3330	26 N/cm ¹

¹ 304 mm/min (12 in/min)

Static Shear

Test Method: ASTM D3654

Temperature	Value
23 °C	1,000 g ¹
49 °C	750 g ¹
70 °C	500 g ¹

¹ 13 x 25 mm (0.5 x 1 in) sample area, test terminated at 10,000 minutes

Attribute Name	Value
Short Term Temperature Resistance	100 °C ¹
Long Term Temperature Resistance	80 °C ²

¹ Short Term (minutes, hour)

² Long Term (day, weeks)

Typical Environmental Performance

Attribute Name	Value
Solvent Resistance	No apparent degradation when exposed to splash testing of most hydrocarbon solvents.
UV Resistance	Excellent resistance to direct exposure to sunlight or other sources of ultraviolet (U.V.) light.

Handling/Application Information

Application Examples

- Signs
- Holding Electronic Accessories
- Exhibitions
- Smoke Alarms
- Dispensers
- Air Fresheners
- Point of Purchase and other Displays
- Nameplates
- Picture Frame Tabs

Application Techniques


- Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength.
- To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Typical surface cleaning solvents are isopropyl alcohol (rubbing alcohol) and water or heptane. Note: Carefully read and follow manufacturer's precautions and directions for use when using solvents.
- Ideal tape application temperature is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive may become too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.

Removal Techniques


For rigid surfaces, lever or pry apart the substrates to break the bond.



For flexible surfaces, peel back slowly to ensure clean removal.



To remove tape from substrate, pull back corner and peel off quickly.



Design Considerations

- As a general rule, four square inches of tape should be used for each pound of weight to be supported in static load. More or less tape may be required depending upon the particular application. User evaluation is, therefore, required to determine optimal tape usage.
- Care should be used when bonding to surfaces with very low internal strength such as painted plaster board, fabric or cloth, wallpaper, blown vinyl, etc. since delamination of that surface may occur.
- Care should also be taken with wood veneers and highly polished wood as very glossy surfaces may leave an image when the tape is removed.

Storage and Shelf Life

Store under normal conditions of 16° to 27°C (60° to 80°F) and 40 to 60% relative humidity in the original packaging, out of direct sunlight. For best performance, use this product within 24 months from date of manufacture.

Available Sizes

Attribute Name	Value
Maximum Available Width	1.18 mm
Maximum Length	160 m
Normal Slitting Tolerance	±0.8 mm

Available Sizes - Detailed

1/2 in x 27 yd (12 mm x 25 m)
3/4 in x 27 yd (19 mm x 25 m)
1 in x 27 yd (25 mm x 25 m)

Automotive Disclaimer

Select Automotive Applications:
This product is an industrial product and has not been designed or tested for use in certain automotive applications, such as automotive electric powertrain battery or high voltage applications, which may require the product to be manufactured in a IATF certified facility, meet a Ppk of 1.33 for all properties, undergo an automotive production part approval process (PPAP), or fully adhere to automotive design or quality system requirements (e.g., IATF 16949 or VDA 6.3). Customer assumes all responsibility and risk if customer chooses to use this product in these applications.

Information

Precautionary Information: Refer to product label and Material Safety Data Sheet for health and safety information before using the product. For information, please contact your local 3M Office. You can click or scan QR code to see contact detail or visit www.3M.com Important Information: All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law. Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations.

ISO Statement

This product was manufactured under a 3M quality system registered to ISO 9001 standards.

3M™ Centre
Cain Rd, Binfield, Bracknell RG12 8HT, United Kingdom
3m.co.uk/iatd

3M is a trademark of 3M Company.
©3M 2024 (9/24)