



PRODUCT-DETAILS

OTP63A6B

OTP63A6B Safety switch



General Information

Extended Product Type	OTP63A6B
Product ID	1SCA022485R6280
EAN	6417019154756
Catalog Description	OTP63A6B Safety switch

Long Description

Safety switch, 6-p. 415V AC23 63A, 30kW. Mounted auxiliary contact: 1NO0NC. Plastic enclosure. IP65. RedYellow Pistol handle. Interlocked cover. Defeatable interlocking. The enclosure in the OTP series is using a rigid glass reinforced polycarbonate enclosure. The enclosure is UV protected, protected against low-pressure water jets (IP65), and hence built for outdoor and indoor use. The cable entries are for I-flanges and have knock out holes, both from top and bottom. The handle is padlockable and made for three padlocks. The interlocking can be by-passed, for thermographing etc. The switch is made for 5 wire system, and have a fixed neutral terminal and PE terminal.

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	1SCC340076D0201

RoHS Declaration	1SCC340075D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	1SCC340095D0201

Popular Downloads

Data Sheet, Technical Information	1SCC340015C0201
Instructions and Manuals	1SCC340002M0012

Environmental

Degree of Protection	acc. to IEC 60529 IP65
Pollution Degree	3

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030
Last Ordering Date	2026-08-31 All Countries
Replacement Product ID (NEW)	OTP63GA6B
Country or Territory of Origin	Finland

Dimensions

Product Net Width	200 mm
Product Net Height	400 mm
Product Net Depth / Length	140 mm
Product Net Weight	2.2 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	213 mm
Package Level 1 Depth / Length	417 mm
Package Level 1 Height	197 mm
Package Level 1 Gross Weight	2.4 kg
Package Level 1 EAN	6417019154756

Technical

Cable Cross-Section	10 ... 70 mm ²
Cable Entry Position	Top and/or Bottom
Cable Outlets Per Side	I-flange / I-flange
Color	RAL7035
Connecting Capacity	Screw Clamp 10 ... 70 mm ²

Main Circuit	Screw Clamp / PE Terminal 4pc,10 ... 70 mm ²
Conventional Thermal Current (I _{the})	Fully Enclosed 115 A
Degree of Protection	acc. to IEC 60529 IP65
Enclosure Material	Plastic
Handle Color	Red / Yellow
Handle Type	Pistol handle
Impact Resistance Rating	Housing IK08
Maximum Mounted Auxiliary Contacts	2 NO, 2 NC
Mounted Auxiliary Contacts	1 NO, 0 NC
Neutral Type	Fixed Neutral
Number of Auxiliary Contacts NC	0
Number of Auxiliary Contacts NO	1
Number of Poles	6P
Pollution Degree	3
Power Loss	at Rated Operating Conditions per Pole 4 W
Rated Insulation Voltage (U _i)	acc. to IEC/EN 60664-1 750 V
Rated Operational Current AC-22A (I _e)	(380 ... 415 V) 63 A (500 V) 63 A (690 V) 63 A
Rated Operational Current AC-23A (I _e)	(380 ... 415 V) 63 A (500 V) 50 A (690 V) 35 A
Rated Operational Power AC-23A (P _e)	(380 ... 415 V) 30 kW (500 V) 30 kW (690 V) 30 kW
Rated Operational Voltage	Main Circuit 750 V
Rated Short-Circuit Making Capacity (I _{cm})	(690 V AC) 3.6 kA
Rated Short-time Withstand Current Low Voltage (I _{cw})	for 1 s 2.5 kA
Standards	IEC 60947-1, -3
Tightening Torque	Main Circuit 6 N·m
Wire Stripping Length	20 mm

Technical UL/CSA

Wire Stripping Length	20 mm
Tightening Torque	Main Circuit 6 N·m

Certificates and Declarations

BV Certificate	1SCC340018D0204
Declaration of Conformity - CE	1SCC340003D2704
DNV GL Certificate	1SCC340045D0203

External Classifications and Standards

Object Classification Code	Q
ETIM 9	EC000216 - Switch disconnector (low voltage)
ETIM 10	EC000216 - Switch disconnector (AC)
UNSPSC	39122205
IDEA Granular Category Code (IGCC)	5166 >> Safety switch
eClass	V11.1 : 27371403
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Enclosed Switches → Enclosed Safety Switches → Enclosed Safety Switches

