

MOTION CONNECT 500

Article No. : 6FX5002-8QE21-1AD0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

| Electrical data                          |                          |
|------------------------------------------|--------------------------|
| No. of cores x cross-section mm²         | 4x2,5 + 4x0,2 + 2x1,5C C |
| Test voltage, rms Power conductors       | 1.5 kV                   |
| Test voltage, rms Signal conductors      | 0.5 kV                   |
| Type with braking lead                   | Yes                      |
| Rated voltage V0/V according to EN 50395 | 600 V/1000 V             |

| Mechanical data                         |                         |
|-----------------------------------------|-------------------------|
| Type of connection cable engine side    | Connector SPEED-CONNECT |
| Connector size                          | 1 / M23                 |
| Type of bolting                         | not relevant            |
| Type of connection cable converter side | Coupling SPEED-CONNECT  |
| Maximum cable outer diameter            | 13.7 mm                 |
| Length                                  | 3.0 m                   |
| Weight (without connector)              | 0.9 kg                  |

| Static deployment                                  |                         |
|----------------------------------------------------|-------------------------|
| Smallest bending radius (fixed installation)       | 33.2 mm                 |
| Tensile load for permanently installed cable, max. | 50 N/mm² (7252 lbf/in²) |
| Torsional stress                                   | Absolute 30°/m          |

| Dynamic deployment                                                 |                         |
|--------------------------------------------------------------------|-------------------------|
| Smallest bending radius(flexible installation in a cable carriers) | 133.0 mm                |
| Acceleration horizontal, max                                       | 2.0 m/s²                |
| Maximum traversing velocity                                        | 30.0 m/min              |
| Travel path                                                        | 5 m                     |
| Number of bends, max.                                              | 100,000                 |
| Tensile load for moving cable, max.                                | 20 N/mm² (2901 lbf/in²) |

| Technical data                                          |                                                              |
|---------------------------------------------------------|--------------------------------------------------------------|
| Ambient temperature                                     |                                                              |
| Operation with permanently installed cable              | -20.0 ... 80.0 °C<br>Module-end power connector 0 ... 55°C   |
| Operation with moving cable                             | 0.0 ... 60.0 °C<br>Module-end power connector 0 ... 55°C     |
| Storage                                                 | -20.0 ... 80.0 °C<br>Module-end power connector -20 ... 70°C |
| Kind of connection cable                                | Extension                                                    |
| Material of the cable sheath                            | PVC DESINA color orange RAL 2003                             |
| Type of insulation                                      | CFC/silicone-free                                            |
| Standard for behavior in fire: flame resistance         | EN 60332-1-1 to 1-3                                          |
| Oil resistance                                          | EN 60811-2-1 (mineral oil only)                              |
| Verification of suitability as authorisation for USA    | UL758                                                        |
| Verification of suitability as authorisation for Canada | CSA-C22.2-N.210.2-M90                                        |