

特点

- 提供各种螺纹尺寸
- 高质量螺纹设计
- 头高度等于柄直径
- 比钛材质更经济高效

RS M6 Pro 35mm 内六角带帽螺钉、本色 1Stainless 钢

RS 号: 187-1443



RS 认证产品为您提供所有产品类别的专业品质部件。我们的产品系列经过工程师测试、提供与领先品牌相当的质量、而无需支付高昂的价格。

商品描述属性

RS PRO 为您提供一系列六角帽头沉头螺丝。凭借其窄头和修长的外形，它们非常适合用于难以触及的区域。所有螺纹沉头螺丝在其应用范围内均持久耐用，尤其是这些 A4 不锈钢型号。所有型号均高度可靠且质量极佳

一般规格

螺纹尺寸	M6
头部形状	六角套筒盖
材料	不锈钢
表面	普通
螺纹类型	公制
应用	木材加工、家用应用、紧固件和固定件、机器工具和维修、安全防护、面板制造

机械规格

长度	35mm
不锈钢类型	316 A4
螺距	1mm
螺纹公差	6g

操作环境规格

最高温度	300°C
------	-------

认证

合规性 / 认证

rohs 符合性证书, ISO4762, ansi B18, DIN912




Please view our full range listing below for all A4 316 Stainless Steel Self-Colour Hexagon Socket Cap Head Screws:

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Stainless Steel	M3	6 mm	1871207
Hex Socket Cap	Stainless Steel	M3	8 mm	1871213
Hex Socket Cap	Stainless Steel	M3	10 mm	6604636
Hex Socket Cap	Stainless Steel	M3	12 mm	1871229
Hex Socket Cap	Stainless Steel	M3	16 mm	1871235
Hex Socket Cap	Stainless Steel	M3	20 mm	3044429
Hex Socket Cap	Stainless Steel	M3	25 mm	3044435
Hex Socket Cap	Stainless Steel	M3	30 mm	3044615
Separator				
Hex Socket Cap	Stainless Steel	M4	8 mm	1871241
Hex Socket Cap	Stainless Steel	M4	10 mm	6604639
Hex Socket Cap	Stainless Steel	M4	12 mm	1871257
Hex Socket Cap	Stainless Steel	M4	16 mm	1871263
Hex Socket Cap	Stainless Steel	M4	20 mm	1871279
Hex Socket Cap	Stainless Steel	M4	25 mm	1871285
Hex Socket Cap	Stainless Steel	M4	30 mm	1871308
Hex Socket Cap	Stainless Steel	M4	40 mm	3044609
Hex Socket Cap	Stainless Steel	M4	50 mm	3044592
Separator				
Hex Socket Cap	Stainless Steel	M5	8 mm	6604633
Hex Socket Cap	Stainless Steel	M5	10 mm	3044586
Hex Socket Cap	Stainless Steel	M5	12 mm	1871314
Hex Socket Cap	Stainless Steel	M5	16 mm	1871320
Hex Socket Cap	Stainless Steel	M5	20 mm	1871336
Hex Socket Cap	Stainless Steel	M5	25 mm	1871342
Hex Socket Cap	Stainless Steel	M5	30 mm	1871364
Hex Socket Cap	Stainless Steel	M5	40 mm	1871370
Hex Socket Cap	Stainless Steel	M5	50 mm	3044570
Hex Socket Cap	Stainless Steel	M5	60 mm	3044564

Head Shape	Material	Thread Size	Length	RS Part No.
Hex Socket Cap	Stainless Steel	M6	10 mm	6604642
Hex Socket Cap	Stainless Steel	M6	12 mm	1871386
Hex Socket Cap	Stainless Steel	M6	16 mm	1871392
Hex Socket Cap	Stainless Steel	M6	20 mm	1871409
Hex Socket Cap	Stainless Steel	M6	25 mm	1871421
Hex Socket Cap	Stainless Steel	M6	30 mm	1871437
Hex Socket Cap	Stainless Steel	M6	35 mm	1871443
Hex Socket Cap	Stainless Steel	M6	40 mm	1871459
Hex Socket Cap	Stainless Steel	M6	45 mm	6604645
Hex Socket Cap	Stainless Steel	M6	50 mm	1871465
Hex Socket Cap	Stainless Steel	M6	60 mm	3044558
Hex Socket Cap	Stainless Steel	M8	16 mm	1871471
Hex Socket Cap	Stainless Steel	M8	20 mm	1871487
Hex Socket Cap	Stainless Steel	M8	25 mm	1871493
Hex Socket Cap	Stainless Steel	M8	30 mm	1871500
Hex Socket Cap	Stainless Steel	M8	35 mm	1871516
Hex Socket Cap	Stainless Steel	M8	40 mm	1871522
Hex Socket Cap	Stainless Steel	M8	45 mm	6604649
Hex Socket Cap	Stainless Steel	M8	50 mm	1871538
Hex Socket Cap	Stainless Steel	M8	60 mm	1871544
Hex Socket Cap	Stainless Steel	M8	70 mm	6604658
Hex Socket Cap	Stainless Steel	M8	80 mm	6604651

Hex Socket Cap	Stainless Steel	M10	20 mm	3044542
Hex Socket Cap	Stainless Steel	M10	25 mm	6604655
Hex Socket Cap	Stainless Steel	M10	30 mm	3044520
Hex Socket Cap	Stainless Steel	M10	40 mm	3044514
Hex Socket Cap	Stainless Steel	M10	50 mm	3044508
Hex Socket Cap	Stainless Steel	M10	70 mm	3044485
Hex Socket Cap	Stainless Steel	M12	30 mm	3044463
Hex Socket Cap	Stainless Steel	M12	40 mm	3044457
Hex Socket Cap	Stainless Steel	M12	50 mm	3044441



Head Diameter d2 based on Knurled Head

Thread Size d1	M36		(M39)		M42		(M45)		M48		M56		M64	
Thread Pitch	4		4		4.5		4.5		5		5.5		6	
Thread Length b	84		NA		96		NA		108		124		140	
Head Dia. d2	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	53.54	54.46	57.54	58.46	62.54	63.46	66.54	67.46	71.54	72.46	83.46	84.54	95.46	96.54
ISO 4762 (1997)	53.54	54.46			62.54	63.46			71.54	72.46	83.46	84.54	95.46	96.54
ANSI B 18.3.1 M (1986)	53.37	54.46			62.31	63.46			71.27	72.46				
Head Height k	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	35.38	36.00	38.38	39.00	41.38	42.00	44.38	45.00	47.38	48.00	55.26	56.00	63.26	64.00
ISO 4762 (1997)	35.38	36.00			41.38	42.00			47.38	48.00	55.26	56.00	63.26	64.00
ANSI B 18.3.1 M (1986)	35.64	36.00			41.61	42.00			47.58	48.00				
Key Size nominal s	27		27		32		32		36		41		46	
	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
DIN 912 (1983)	27.065	27.275	27.065	27.275	32.08	32.33	32.08	32.33	36.08	36.33	41.08	41.33	46.08	46.33
ISO 4762 (1997)	27.065	27.275			32.08	32.33			36.08	36.33	41.08	41.33	46.08	46.33
ANSI B 18.3.1 M (1986)	27.065	27.319			32.080	32.461			36.080	36.461				
Key Engagement t	min.		min.		min.		min.		min.		min.		min.	
DIN 912 (1983)	19		22		24		24		28		34		38	
ISO 4762 (1997)	19				24				28		34			
ANSI B 18.3.1 M (1986)	18				21				24					
Thread Size d1	M72		M80		M90		M100							
Thread Pitch	6		6		6		6							
Thread Length b	156		172		192		212							
Head Dia. d2	min.	max.	min.	max.	min.	max.	min.	max.						
DIN 912 (1983)	107.46	108.54	119.46	120.54	134.37	135.63	149.37	150.63						
Head Height k	min.	max.	min.	max.	min.	max.	min.	max.						
DIN 912 (1983)	71.26	72.00	79.26	80.00	89.13	90.00	99.13	100.00						
Key Size nominal s	55		65		75		85							
	min.	max.	min.	max.	min.	max.	min.	max.						
DIN 912 (1983)	55.10	55.40	65.10	65.40	75.10	75.40	85.12	85.47						
Key Engagement t	min.		min.		min.		min.							
DIN 912 (1983)	43		48		54		60							
Property Class	12.9		8.8sd 16mm		8.8sd 16mm		10.9		A2 /A4-50		A2 /A4-70		A2 /A4-80	
Tensile Strength	176900 psi		116000 psi		120350 psi		150800 psi		72500 psi		101500 psi		116000 psi	
Yield Strength	159500 psi		92800 psi		95700 psi		136300 psi		30450 psi		65250 psi		87000 psi	
Rockwell Hardness (HRC)	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.	min.	max.
	39	44	22	32	23	34	32	39	NA	NA	NA	NA	NA	NA

Property Class	Steel	Steel	Stainless Steel
	12.9	8.8 & 10.9	A2 & A4
Finish	Furnace Black		Plain
Thread Tolerance	5g6g		6g

Diameters & Lengths With () are not recommended for new design.
 M1.4, 2.6, 39 and 45 are no longer included in DIN 912.
 M1.4, 2.6, 18, 22, 27, 33, 35, and 45 are no longer included in ISO 4762.
 The basic difference between DIN 912-12.9 (1983) / ISO 4762-12.9 (1997) and ANSI B 18.3.M (1986) is both DIN and ISO have a thread tolerance of 5g6g, while ANSI has a thread tolerance of 4g6g, which may not be readily available on a worldwide basis.
 ANSI B 18.3.1 M is only available in Property Class 12.9.

For More Detailed Information, Please Refer To Complete DIN, ISO, or ANSI Standard, Which Are The Governing Standards.
 DIN 912 (1983) / ISO 4762 (1997) / ANSI B 18.3.1M (1982) - LGF 05/01/08 See Next Page For Additional Information