


Castor D75 fixed



REACH RoHS

The D75 castor series (castor diameter 75 mm) has a robust metal housing and a castor that can support a load of 60 kg. The D75 fixed castor has a narrow screw-on plate with an anti-torsion block. This allows it to be mounted in the groove of a profile.



Scope of Delivery

Sheet-metal housing, bright zinc-plated, black
Wheel axle with ball bearing,
Anti-torsion block,
Dust shield,
Tyres TPE, 80 Sh A, grey

Technical note

[0.0.420.12](#) For more information, please click here!

Properties	
Article number	0.0.420.12
Delivery unit	1 pce.
Weight	260.0 g
Load-carrying capacity	60 kg/Castor

Accessoires