

## Vac Pump Oil



Food grade, high performance, vacuum pump oil

### Product Overview

ROCOL® Vac Pump Oil is a non-toxic, ISO VG 100, high performance vacuum oil formulated to maximise lubricant lifetime, even under conditions of high load and elevated temperature.

ROCOL® Vac Pump Oil has a low vapour pressure to enhance pump efficiency and is suitable for use with a wide range of vacuum pump formats particularly those found in food, pharmaceutical and other clean environments where NSF H1 lubricants are required.

ROCOL® Vac Pump Oil is also an extremely efficient Flushing Oil.

### Features and Benefits

- ROCOL® Vac Pump Oil offers an excellent wide temperature resistance of -5°C to +130°C.
- ROCOL® Vac Pump Oil minimises deposits in vacuum pump systems for increased pump reliability and efficiency.
- High performance oil formulated to maximise lubricant lifetime, even under conditions of high load and elevated temperature.
- ROCOL® Vac Pump Oil prevents corrosion often experienced in vacuum pumps due to moisture ingress.
- Non-toxic, NSF H1 registered oil for use where incidental contact with foodstuffs may occur.
- ROCOL® Vac Pump Oil is a clean low odour product.
- Biologically hard formulation - resists bacterial growth.

### Directions for Storage and Use

- For optimum performance drain & flush the vacuum pump sump prior to filling with ROCOL® Vac Pump Oil.
- Flushing with ROCOL® Vac Pump Oil :
  - Run gearbox to warm up old oil
  - Drain off old oil
  - Fill with Vac Pump Oil to correct level
  - Run off-load for 10-20 mins
  - Drain and fill with correct oil
- The storage temperature should be controlled between +1°C and +40°C.
- Shelf life is 3 years from date of manufacture.

### Specifications

- ROCOL® Vac Pump Oil does not contain: animal derived materials, nut oils or genetically modified ingredients.
- FDA Group 21 CFR 178.3570
- NSF H1 registered – 137855

### Pack Sizes

Pack Size	Part Code
5 L	16806
20 L	16805



# Technical Data

**ROCOL**<sup>®</sup>

Performance you can trust



## Vac Pump Oil

Food grade, high performance, vacuum pump oil

Property	Test Method	Result
Appearance		colourless liquid
Base Type		High purity base fluid
Kinematic Viscosity at 40°C	IP 71 (ASTM D445)	100 cSt
Odour		Barely perceptible
Temperature Range - Standard		-5°C to +130°C
Flash Point	ASTM D92	>240°C
Specific Gravity		0.86

Values quoted above are typical and do not constitute a specification.

### Safety Data Sheets

Safety data sheets are available for download from our website [www.rocol.com](http://www.rocol.com) or may be obtained from your usual ROCOL contact.

The information in this publication is based on our experience and reports from customers. There are many factors outside our control or knowledge which affect the use and performance of our products, for which reason it is given without responsibility.

Issue 06-10

T +44 (0) 113 232 2600  
F +44 (0) 113 232 2740  
E [customer-service@rocol.com](mailto:customer-service@rocol.com)  
[www.rocol.com](http://www.rocol.com)

ROCOL House, Swillington, Leeds LS26 8BS

Registered Company No. 559693 VAT No. 742 0531 67

Registered Office: Admiral House, St Leonard's Road, Windsor, Berkshire SL4 3BL

ROCOL A division of **ITW** Ltd



BS EN ISO 9001  
Certificate No. FM 12448



BS EN ISO 14001  
Certificate No. EMS 67596



OHSAS 18001  
Certificate No. OHS 78173



INVESTOR IN PEOPLE