EDSP06SGRNNTR04 ✔ ACTIVE



Alcoswitch | Alcoswitch DIP EDSP

TE Internal #: 3-2319764-8

DIP Switch, Gold Flash Contact Plating, Black, High Temperature Nylon, 6 Switch, -20 – 85 °C, Piano (Side Actuated), Alcoswitch DIP EDSP

View on TE.com >

Switches > DIP & SIP Switches



DIP & SIP Switch Type: **DIP**

Switch Contact Plating Material: **Gold Flash**

Case Color: **Black**

Case Material: **High Temperature Nylon**

Sealed Device: **No**

Features

Product Type Features

DIP & SIP Switch Type	DIP
Sealed Device	No
Actuator Style	Piano (Side Actuated)

Configuration Features

Number of Positions	6
Number of Switches	6
Configuration (Pole-Throw)	Single Pole - Single Throw

Electrical Characteristics

Contact Current Rating	.025 A
Operating Voltage	24 VDC

Body Features

Actuator Color	White
Product Orientation	Vertical
Case Color	Black

Case Material	High Temperature Nylon

Contact Features

Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold Flash
Switch Contact Plating Material	Gold Flash
Contact Base Material	Copper Alloy

Termination Features

Termination Method to PCB	Surface Mount

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Product Length	15.14 mm[.596 in]
Product Height	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-20 – 85 °C

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	700

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts




TE Part # 2319764-2
E STACK PIANO 4P G LONG TUBE PD ON




TE Part # 2319764-4
E STACK PIANO 8P G LONG TUBE PD ON



TE Part # 3-2319764-1
E STACK PIANO 2P G LONG T&R PD ON




TE Part # 3-2319764-3
E STACK PIANO 6P G LONG T&R PD ON



TE Part # 4-2319764-1
E STACK PIANO 2P G LONG T&R PD OFF

Also in the Series | Alcoswitch DIP EDSP




DIP & SIP Switches(20)

Customers Also Bought




TE Part #1623932-6
CFR50 5% 100R



TE Part #1879666-6
H8 150K 0.1% 15PPM



TE Part #7-1625892-7
3W SM M/OX 5% 18K



TE Part #1-1623788-7
SQM5 68R 5% (WIRE)



TE Part #3-1623931-7
CFR25 5% 47R



TE Part #6-1879233-7
SMW5 56R 5%



TE Part #1623234-1
CRG0805 1% 47K



TE Part #5-1623930-2
CFR25 5% 220K



TE Part #6-1623931-6
CFR25 5% 6K8



TE Part #2176231-8
3522 20R 1% 3W

Documents

Product Drawings

E STACK PIANO 6P G SHORT T&R PD ON

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-2319764-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_3-2319764-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_3-2319764-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

SWITCHES_CORE_PROGRAM_CATALOG

English