

# SACC-CI-M12FSM-5PE-L180 THR R - Contact carrier



1420833

<https://www.phoenixcontact.com/gb/products/1420833>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Power, 6-position, Socket, straight, M12, coding: M, PCB mounting, THR solder connection, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

## Your advantages

- For compact devices: transmit high power in a confined space
- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration, thanks to mechanical port screw connections with threaded fastening
- Additional gasket for the device when not plugged in

## Commercial data

Item number	1420833
Packing unit	60 pc
Minimum order quantity	60 pc
Sales key	ABQAGX
Product key	ABQAGX
GTIN	4055626280608
Weight per piece (including packing)	10.8 g
Weight per piece (excluding packing)	3.245 g
Customs tariff number	85366990
Country of origin	DE

## Technical data

### Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

### Product properties

Product type	Contact insert
Application	Power
Sensor type	Power
Number of positions	6
Connection profile	5+PE
No. of power contacts	5
Seal present	yes
Coding	M
Thread type	M12

### Insulation characteristics

Overvoltage category	III
Degree of pollution	3

### Electrical properties

Rated surge voltage	6 kV
Nominal voltage $U_N$	630 V
Nominal current $I_N$	8 A

### Connection data

Connection method	THR solder connection
-------------------	-----------------------

### Interfaces

Signal type/category	Power
----------------------	-------

### Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA 4T

### Connector

#### Connection 1

# SACC-CI-M12FSM-5PE-L180 THR R - Contact carrier



1420833

<https://www.phoenixcontact.com/gb/products/1420833>

Head design	Socket
Head cable outlet	straight
Head thread type	M12
Coding	M

## Cable/line

Signal type/category	Power
----------------------	-------

## Mechanical properties

### Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked) IP67, when plugged in
Ambient temperature (operation)	-25 °C ... 105 °C -40 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

## Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-111

## Mounting


Mounting type	PCB mounting
---------------	--------------

## Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad

## Drawings

Schematic diagram



Pin assignment of M12 socket, 6-pos., M-coded, socket side view

# SACC-CI-M12FSM-5PE-L180 THR R - Contact carrier




1420833

<https://www.phoenixcontact.com/gb/products/1420833>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1420833>

	<b>cULus Recognized</b> Approval ID: E468743-20180113			
	Nominal voltage $U_N$	Nominal current $I_N$	Cross section AWG	Cross section $\text{mm}^2$
	600 V	10 A	-	-

# SACC-CI-M12FSM-5PE-L180 THR R - Contact carrier



1420833

<https://www.phoenixcontact.com/gb/products/1420833>

## Classifications

### ECLASS

ECLASS-13.0	27440110
-------------	----------

### ETIM

ETIM 9.0	EC002637
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

1420833

<https://www.phoenixcontact.com/gb/products/1420833>

## Environmental product compliance

## EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

## China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

## EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	2784dbbf-2e53-41ee-8c0d-fd00bd7d5b72

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)