




ZM75

Precision locknut

Precision locknut ZM, accessory ZM..

Technical information



Main Dimensions & Performance Data

|                 |             |                           |
|-----------------|-------------|---------------------------|
| d               | M75X2       | Thread                    |
| D               | 98 mm       | Outside diameter          |
| h               | 18 mm       | Height                    |
| M <sub>A</sub>  | 15 Nm       | Mounting torque set screw |
| F <sub>aB</sub> | 331,000 N   | Breaking load, axial      |
| M <sub>L</sub>  | 260 Nm      | Breakawag                 |
| M <sub>AL</sub> | 150 Nm      | Mounting torque reference |
| M <sub>M</sub>  | 8.41 kg*cm2 | Mass moment of inertia    |

≈m 0.423 kg Weight

Dimensions

|                |        |                         |
|----------------|--------|-------------------------|
| d <sub>1</sub> | 90 mm  | Plant diameter outside  |
| t              | 3.5 mm | Hight retaining slot    |
| b              | 8 mm   | Width retaining slot    |
| c              | 9 mm   | Distance bore           |
| m              | M8     | Threaded - threaded pin |