




LGH

TE Internal #: 3-848075-5

1 Position Circular Power Connector, Lead Assembly, 30000 VDC, 16 AWG, Wire-to-Wire, Wire & Cable, Socket, -55 – 125 °C [-67 – 257 °F]

[View on TE.com >](#)

Connectors > Power Connectors > Circular Power > Circular Power Connectors



Number of Positions: 1

Connector Product Type: **Lead Assembly**

Operating Voltage: **30000 VDC**

Wire Size: **16 AWG**

Connector System: **Wire-to-Wire**

Features

Product Type Features

Connector Product Type	Lead Assembly
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Operating Voltage	30000 VDC
-------------------	-----------

Body Features

Positive Stop Ferrule	Without
-----------------------	---------

Contact Features

Contact Type	Socket
Contact Protection	Without

Termination Features

Termination Method to Wire & Cable	Pre-Terminated to Cable
------------------------------------	-------------------------

Mechanical Attachment

Mating Alignment	With
------------------	------



Dimensions

Wire Size	16 AWG
Assembly Length	889.9 mm[35 in]

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Shielded	No
----------	----

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) SVHC > Threshold: Pb (.6% in 74020097) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Customers Also Bought

TE Part #E00553N001
502K033/S(S15)

TE Part #C51949-000
HX-SCE-1K-25.4-50-S1-4

TE Part #CAT-T3437-T548
TMS-SCE Military Grade Sleeves

TE Part #CAT-R21-731072
Bulbous Heat Shrink Boots: Lipped, Straight

TE Part #CAT-T3437-H647
HLX Low Fire Hazard Markers

TE Part #170225-1
RING TERMINAL

TE Part #4-1879627-2
H4P 510R 1% 100PPM

Documents

Product Drawings
LGH-2 LEAD DBL MLD END
English

Datasheets & Catalog Pages
1308940_Sec9_lghlead
English