




R(D)Q, Compact Cylinder, Air Cushion RQB20-20

Datasheet

General series information


- Unique air cushion construction with no cushion ring.
- Wide size variations from $\varnothing 20$ to $\varnothing 100$.
- Nearly three times the allowable kinetic energy.
- Improved noise reduction (Stroke end impact noise reduced) and repeatability.
- Interchangeable mounting.

Standard specifications

Magnet	None
Mounting	B [Through Hole (Standard)]
Bore Size	20 mm
Port Thread	Rc
Stroke	20
Body Option	Rod End Female Threads (Standard)
Auto Switch	No Switch
Lead Wire or Prewired Connector	0.5m (Or None in the Case of No Switch)
Number	2 pcs. (Or None in the Case of No Switch)
Maximum operating pressure	1.0 MPa
Minimum operating pressure	0.05 MPa
Proof pressure	1.5 MPa
Maximum piston speed	500 mm/s
Type of cushioning	Pneumatic (non-lube) type
Female thread of rod end	Female threads
Minimum piston speed	50 mm/s
Fluid	Air
Ambient and fluid temperature	-10°C to 70°C (with no freezing)

Stroke length tolerance	+1.0 0
F449 - Rod_end_thread_tolerance	JIS class 2
F450 - Mounting	Through hole
Weight	0.180 Kg

Dimensions



Specifications are subject to change without prior notice and any obligation on the part of the manufacturer.

Additional information

Catalogue

[RQ_EU.pdf](#)

Operation manuals

[RQ_OP_Manual_RQxx-OM0002G.pdf](#)