

Technical data


32928XU

Single row tapered roller bearings

Tapered roller bearing, pressed steel cage



VISUAL (S)



PRODUCT DEFINITION	
Brand	NTN
d - Internal diameter	140 mm
D - External diameter	190 mm
B - Bearing/Inner ring width	32 mm
C - Outer ring width	25 mm
T - Total width	32 mm
d1 - External diameter inner ring	165 mm
a - Charge load application point	34 mm
rs - Min fillet radius	2 mm
r1s - Min fillet radius	1,5 mm
Mass	2,5 kg
ISO 355 reference	T2CC140

PRODUCT PERFORMANCE	
C - Dynamic load	221000000 mN
C0 - Static load	375000000 mN
Cu - Fatigue limit load	39000000 mN
A2 - Rating life coefficient	1
e - Coefficient	0.36
Y0 - Static axial load coefficient	0.92
Y2 - Upper axial load coefficient	1.67
N lim - Oil lubrication limit speed	13200 °/s
N lim - Grease lubrication limit speed	10200 °/s
Tmin - Min operating temperature	233,15 °K



PRODUCT PERFORMANCE

Tmax - Max operating temperature	393,15 °K
---	-----------

ABUTMENT

da max - Max shoulder diameter IR	150 mm
db min - Min IR shoulder diameter	150 mm
Da min - Min shoulder diameter OR	177 mm
Da max - Max shoulder diameter OR	181,5 mm
Db min - Min OR shoulder diameter	184 mm
Ca - Min clearance	6 mm
Cb - Min clearance	6 mm
ra max - Max fillet radius	2 mm
r1a - Max fillet radius	1,5 mm



INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$F_a / F_r \leq e$		$F_a / F_r > e$	
X	Y	X	Y
1	0	0.4	Y2

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.5	Y0

If $P_0 \leq F_r$, then use $P_0 = F_r$

The values for e, Y2 and Y0 are shown in the above table

