

# TITAN 850

## DESCRIPTION AND GENERAL PROPERTIES

- **Material** Nitrile GRIP&PROOF coating
- **Length (cm)** 23.5 - 27.5
- **Wrist** Safety cuff
- **Colour/Color** Orange
- **Interior finish** Seamless textile support
- **Exterior finish** Ventilated back
- **Size / EAN** 7 8 9 10 11
- **Packaging** 1 pair/bag - 12 pairs/bag - 48 pairs/carton



## PERFORMANCE RESULTS


Certification category 2




4132XP

### Legends

#### EN 388 MECHANICAL HAZARDS



#### EN 407 THERMAL RISKS heat and fire



#### CHEMICAL RISKS

##### EN ISO 374-1 Type A



U V W X Y Z

- A Methanol
- B Acetone
- C Acetonitrile
- D Dichloromethane
- E Carbon Disulfide
- F Toluene
- G Diethylamine
- H Tetrahydrofurane
- I Ethyl acetate

##### EN ISO 374-1 Type B



X Y Z

- J n-Heptane
- K Sodium hydroxide 40%
- L Sulphuric acid 96%
- M Nitric acid 65%
- N Acetic acid 99%
- O Ammonia 25%
- P Hydrogen peroxide 30%
- S Hydrofluoric acid 40%
- T Formaldehyde 37%

##### EN ISO 374-1 Type C



CUT

#### CUT RESISTANCE

- |             |             |             |
|-------------|-------------|-------------|
| A1 ≥ 200 G  | A4 ≥ 1500 G | A7 ≥ 4000 G |
| A2 ≥ 500 G  | A5 ≥ 2200 G | A8 ≥ 5000 G |
| A3 ≥ 1000 G | A6 ≥ 3000 G | A9 ≥ 6000 G |

#### MICRO-ORGANISMS

##### EN ISO 374-5



Protection against bacteria, fungi

##### EN ISO 374-5



Protection against bacteria, fungi, virus

VIRUS

##### EN 511



#### GOLD HAZARDS

PERFORMANCE LEVELS

- 0-4 0-4 0 or 1
- Water permeability
- Contact cold resistance
- Convective cold resistance

##### EN 421



RADIOACTIVE CONTAMINATION

For more details: [www.mapa-pro.com](http://www.mapa-pro.com)

**MAPA**  
PROFESSIONNEL

# TITAN 850

## SPECIFIC ADVANTAGES

- Shock protection : specific areas are reinforced to bring cushioning protection and comfort where you need it (Upper thumb, Knuckle, Base fingers & Palm)
- Durability in use : Long lasting coating, gloves stay clean due to their liquid resistance, suppleness guaranteed even after drying
- Grip overtime thanks to our specific technology
- Grease & Oilproof for better skin protection thanks to our specific technology

## MAIN FIELDS OF USE

### Industrial maintenance

- Maintenance

### Installation of industrial equipments

- Assembling of heavy parts
- Maintenance

### Manufacturing

- Assembling of heavy parts
- Handling of thick metal sheets
- Handling oily mechanical parts
- Machine tool manufacturing
- Machining of heavy parts
- Mechanical maintenance
- Metal working

### Industrial equipment / Metal transformation

- Assembling of heavy parts
- Handling heavy metal sheets
- Handling oily mechanical parts
- Machine tool manufacturing
- Mechanical maintenance
- Metal working
- Machining of heavy parts

### Mining / Utilities / Transportation

- Maintenance

### Transport, logistics

- Goods handling on loading bays, docks, warehousing etc.
- Operating handling equipment
- Order preparation

## INSTRUCTIONS FOR USE

### Instructions for use

Nitrile gloves are not recommended for use by those sensitive to dithiocarbamates

Avoid contact with ketones and organic nitrogen products

It is recommended that you pre-test the gloves as the actual workplace conditions of use may differ from those of the CE type tests (in particular mechanical and/or chemical), according to temperature, abrasion and degradation.

It is recommended to not use them next to moving machinery.

Make sure that hands are clean and dry before putting the gloves on

### Storage conditions

Store the gloves in their original packaging away from light, heat and electrical installations.

Ensure the inside of the gloves is dry and that they are in good condition before reusing them.

### Laundering conditions

Gloves contaminated with oil or grease should be wiped with a dry cloth before removing them.

Caution: improper use of the gloves or cleaning them in a way that is not specifically recommended can alter their performance levels.

## LEGISLATION

This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council. This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH)

- UE type certificate or CE type examination certificate  
0075/014/162/12/18/2899

- Issued by the notified body nr

CTC - 4 rue Hermann Frenkel - 69367 Lyon Cedex 07 - France  
0075