

VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2



1466777

<https://www.phoenixcontact.com/gb/products/1466777>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Surge arrester for 2-pos. insulated and grounded 1000 V DC PV systems, for DIN rail mounting, 3-pos. base element with remote indication contact, three pluggable temperature-monitored protective elements, status message on each plug.

Your advantages

- Easy and safe installation with forward-thinking handling and safety features
- Reliable system protection with maximum performance and endurance
- Can be used in a wide range of applications due to the optimized design and broad portfolio
- Simple planning due to comprehensive digital data and selectors

Commercial data

Item number	1466777
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CL11E1
Product key	CL11E1
GTIN	4063151862626
Weight per piece (including packing)	389.3 g
Weight per piece (excluding packing)	359 g
Customs tariff number	85363010
Country of origin	DE

VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2



1466777

<https://www.phoenixcontact.com/gb/products/1466777>

Technical data

Product properties

Product type	PV arrester
IEC test classification	PV I / II
	PV T1 / T2
EN type	T1 / T2
IEC power supply system	DC
Type	DIN rail module, two-section, divisible
Number of positions	3
Installation location	Indoor
Installation location of the disconnect device	Internal
Accessibility	Accessible
Connection configuration	Y configuration
End-of-life mode	OCFM (Open-Circuit Failure Mode)
Surge protection fault message	Optical, remote indicator contact

Insulation characteristics

Overvoltage category	III
Pollution degree	2

Electrical properties

Indicator/remote signaling

Connection name	Remote fault indicator contact
Switching function	Changeover contact
Max. required back-up fuse	1 A (gG)
AC operating voltage	5 V AC ... 250 V AC (≤ 2000 m (amsl))
	5 V AC ... 150 V AC ($\leq \text{⬆} \text{⬆} \text{⬆}$ m (amsl))
AC operating current	5 mA AC ... 1 A AC
DC operating voltage	30 V DC ($\leq \text{⬆} \text{⬆} \text{⬆}$ m (amsl))
DC operating current	1 A DC
DC operating voltage	125 V DC ($\leq \text{⬆} \text{⬆} \text{⬆}$ m (amsl))
DC operating current	200 mA DC
Insulation type	The product has double/reinforced insulation between the main and auxiliary circuit.

Connection data

Connection method	Screw connection
Screw thread	M5
Tightening torque	2.5 Nm ... 3 Nm
Stripping length	12 mm
Conductor cross section flexible	1.5 mm ² ... 16 mm ²

VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2



1466777

<https://www.phoenixcontact.com/gb/products/1466777>

	2x 1.5 mm ² ... 6 mm ² (2 conductors with the same cross-section)
Conductor cross section rigid	1.5 mm ² ... 25 mm ²
	2x 1.5 mm ² ... 6 mm ² (2 conductors with the same cross-section)
Conductor cross section AWG	15 ... 4
2 conductors with the same cross section, flexible, with TWIN ferrule with plastic sleeve	1.5 mm ² ... 6 mm ²
Conductor cross section, flexible, with ferrule, with plastic sleeve	1.5 mm ² ... 16 mm ²
	2x 1.5 mm ² ... 6 mm ² (2 conductors with the same cross-section)
Conductor cross section flexible, with ferrule without plastic sleeve	1.5 mm ² ... 16 mm ²
	2x 1.5 mm ² ... 6 mm ² (2 conductors with the same cross-section)

Remote fault indicator contact

Connection method	Screw connection
Screw thread	M3
Tightening torque	0.5 Nm ... 0.6 Nm
Stripping length	7 mm
Conductor cross section flexible	0.25 mm ² ... 1.5 mm ²
Conductor cross section rigid	0.25 mm ² ... 1.5 mm ²
Conductor cross section AWG	24 ... 16
Conductor cross section, flexible, with ferrule, with plastic sleeve	0.25 mm ² ... 1.5 mm ²
Conductor cross section flexible, with ferrule without plastic sleeve	0.25 mm ² ... 0.75 mm ²

Dimensions

Dimensional drawing	
Width	53.4 mm
Height	96.6 mm
Depth	71.5 mm (incl. DIN rail 7.5 mm)
Horizontal pitch	3 Div.

Material specifications

Color	gray (RAL 7042)
	light gray (RAL 7035)
Flammability rating according to UL 94	V-0
CTI value of material	600
Insulating material	PA 6.6-FR 20 % GF
	PBT
Material group	I
Housing material	PA 6.6-FR 20 % GF
	PBT

VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2



1466777

<https://www.phoenixcontact.com/gb/products/1466777>

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Protective circuit

Mode of protection	(DC+) - (DC-)
	(DC+) - PE
	(DC-) - PE
Residual current I_{PE}	$\leq 350 \mu A$ AC
	$\leq 100 \mu A$ DC
Standby power consumption P_C	≤ 120 mVA
Nominal discharge current I_n (8/20) μs	20 kA
Maximum discharge current I_{max} (8/20) μs	40 kA
Impulse discharge current (10/350) μs , charge	2.5 As
Impulse discharge current (10/350) μs , specific energy	6.25 kJ/ Ω
Impulse discharge current (10/350) μs , peak value I_{imp}	5 kA
Total discharge current I_{Total} (8/20) μs	40 kA
Total discharge current I_{Total} (10/350) μs	5 kA
Voltage protection level U_p	≤ 4.2 kV
Residual voltage U_{res}	≤ 4.2 kV (at I_n)
	≤ 3.6 kV (at 10 kA)
	≤ 3.2 kV (at 5 kA)
	≤ 3 kV (at 3 kA)
Response time t_A	≤ 25 ns

PV protective circuit

Connection configuration	Y configuration
End-of-life mode	OCFM (Open-Circuit Failure Mode)

Protective circuit DC voltage side (DC)

Open circuit voltage U_{OCSTC}	1000 V DC
Maximum discharge current I_{max} (8/20) μs	40 kA
Response time t_A	≤ 25 ns
Impulse discharge current (10/350) μs , charge	2.5 As
Impulse discharge current (10/350) μs , specific energy	6.25 kJ/ Ω
Impulse discharge current (10/350) μs , peak value I_{imp}	5 kA
Total discharge current I_{Total} (8/20) μs	40 kA
Total discharge current I_{Total} (10/350) μs	5 kA
Insulation resistance R_{iso}	> 5 M Ω (at 500 V DC)
Nominal discharge current I_n (8/20) μs	20 kA
Continuous operating current I_{CPV}	$\leq 100 \mu A$ DC
Maximum continuous operating voltage U_{CPV}	1200 V DC

VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2



1466777

<https://www.phoenixcontact.com/gb/products/1466777>

Short-circuit current rating I_{SCP}	15000 A
Residual voltage U_{res}	≤ 4.2 kV (at I_n)
	≤ 3.6 kV (at 10 kA)
	≤ 3.2 kV (at 5 kA)
	≤ 3 kV (at 3 kA)
Residual current I_{PE}	≤ 350 μ A AC
	≤ 100 μ A DC
Voltage protection level U_p	≤ 4.2 kV
Standby power consumption P_C	≤ 120 mVA

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20C (Installed)
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Ambient temperature (assembly)	-5 °C ... 50 °C
Altitude	≤ 5000 m (amsl)
Permissible humidity (operation)	5 % ... 95 %
Shock (operation)	25g (Half-sine / 11 ms / 3x \pm X, \pm Y, \pm Z)
Vibration (operation)	5g (5-500 Hz/2.5 h/XYZ)

Standards and regulations

Standards/specifications	EN 61643-31
Note	2019
Standards/specifications	IEC 61643-31
Note	2018

Mounting

Mounting type	DIN rail: 35 mm
---------------	-----------------

VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2




1466777

<https://www.phoenixcontact.com/gb/products/1466777>

Drawings

Dimensional drawing




VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2

1466777

<https://www.phoenixcontact.com/gb/products/1466777>

Circuit diagram



VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2



1466777

<https://www.phoenixcontact.com/gb/products/1466777>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1466777>



IECEE CB Scheme

Approval ID: NL-109183

CCA

Approval ID: NTR NL-8030



KEMA-KEUR

Approval ID: 71-133324

VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2



1466777
<https://www.phoenixcontact.com/gb/products/1466777>

Classifications

ECLASS

ECLASS-13.0	27171402
-------------	----------

ETIM

ETIM 9.0	EC000941
----------	----------

VAL-SPP-T1-1000DC-PV-2+V-UT-R - Lightning/surge arrester type 1/2



1466777

<https://www.phoenixcontact.com/gb/products/1466777>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk