

(!) Discontinued

TeSys LE - enclosure for DOL starter - with pushbutton

Local distributor code: 402711609

2711609 DE1DS1A05

! Discontinued on: 9 Feb 2023

EAN Code: 3389110087086

Main

Range of product	TeSys
Range	TeSys
Device short name	DE1D
Product or component type	Enclosure
Material	Polycarbonate
Device composition	Contactor ordered separately Thermal overload relay ordered separately
Product compatibility	LE1D12 LE1D09
Control type	Push-button reset blue R

Complementary

Cable entry number	2 ISO20 top 2 ISO20 bottom 2 Pg 13 bottom 2 Pg 16 bottom
Height	166 mm
Width	88 mm
Depth	145 mm
Net weight	0.3 kg

Environment

IP degree of protection	IP65 conforming to IEC 60529	
IK degree of protection	IK07 conforming to IEC 60529	
Ambient air temperature for operation	-540 °C	
Environmental characteristic	Standard environment	
Product certifications	LIKCA	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	17.500 cm
Package 1 Width	17.500 cm

Package 1 Length	22.500 cm
Package 1 Weight	506.000 g
Unit Type of Package 2	P06
Number of Units in Package 2	30
Package 2 Height	75.000 cm
Package 2 Width	60.000 cm
Package 2 Length	80.000 cm
Package 2 Weight	28.510 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

∇ Environmental footprint	
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	107
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances		
Packaging made with recycled cardboard	Yes	
Packaging without single use plastic	Yes	
EU RoHS Directive	Compliant	
REACh Regulation	REACh Declaration	

Use Again

○ Repack and remanufacture		
Circularity Profile	End of Life Information	
Take-back	No	