

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** Bailey

**Supplier's address:** Yvo Hendriks, Everdenberg 21, 4902TT Oosterhout, NL

**Model identifier:** 145655

**Type of light source:**

|                                                     |       |                                 |      |
|-----------------------------------------------------|-------|---------------------------------|------|
| Lighting technology used:                           | other | Non-directional or directional: | NDLS |
| Light source cap-type (or other electric interface) | G4    |                                 |      |
| Mains or non-mains:                                 | NMLS  | Connected light source (CLS):   | No   |
| Colour-tuneable light source:                       | No    | Envelope:                       | -    |
| High luminance light source:                        | No    |                                 |      |
| Anti-glare shield:                                  | No    | Dimmable:                       | Yes  |


## Product parameters

| Parameter                                                                                                                                      | Value                | Parameter                                                                                                                                                  | Value                  |
|------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| <b>General product parameters:</b>                                                                                                             |                      |                                                                                                                                                            |                        |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer                                                                  | 10                   | Energy efficiency class                                                                                                                                    | G                      |
| Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 100 in Sphere (360°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 2 700                  |
| On-mode power ( $P_{on}$ ), expressed in W                                                                                                     | 10,0                 | Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal                                                                               | 0,00                   |
| Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal                                                | -                    | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set                                                         | 100                    |
| Outer dimensions without separate control gear, lighting control                                                                               | Height               | Spectral power distribution in the range 250 nm to 800 nm, at full-load                                                                                    | See image in last page |
|                                                                                                                                                | Width                |                                                                                                                                                            |                        |
|                                                                                                                                                | Depth                |                                                                                                                                                            |                        |


|                                                           |   |                                    |                |  |
|-----------------------------------------------------------|---|------------------------------------|----------------|--|
| parts and non-lighting control parts, if any (millimetre) |   |                                    |                |  |
| Claim of equivalent power <sup>(a)</sup>                  | - | If yes, equivalent power (W)       | -              |  |
|                                                           |   | Chromaticity coordinates (x and y) | 0,460<br>0,410 |  |

(a) : not applicable;

(b) : not applicable;



Model placed on the Union market from 01/10/2022



**EPREL registration number:** 1353634

<https://eprel.ec.europa.eu/qr/1353634>

**Supplier:** Bailey, Electric & Electronics B.V. (Manufacturer)

**Website:** [www.bailey.nl](http://www.bailey.nl)

**Customer care service:**

**Name:** Yvo Hendriks

**Website:** [www.bailey.nl](http://www.bailey.nl)

**Email:** [purchase@bailey.nl](mailto:purchase@bailey.nl)

**Phone:** +31 162 522446

**Address:**

Everdenberg 21  
4902TT Oosterhout  
Netherlands