

### Main

|                            |                                                                                                      |
|----------------------------|------------------------------------------------------------------------------------------------------|
| Range of product           | Odace                                                                                                |
| Product or component type  | USB charger                                                                                          |
| Device application         | Charger                                                                                              |
| Device presentation        | Mechanism with fixing frame                                                                          |
| Device mounting            | Flush                                                                                                |
| Type of USB power supply   | USB type A + C                                                                                       |
| Integrated connection type | 1 USB type A 5 V DC, maximum load current: 2.4 A<br>1 USB type C 5 V DC, maximum load current: 2.4 A |
| Condition of use           | Indoor                                                                                               |

### Complementary

|                                |                                                                                                                                                                                                                                                                                                                                     |
|--------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Colour tint                    | Aluminium                                                                                                                                                                                                                                                                                                                           |
| Output current                 | 2.4 A                                                                                                                                                                                                                                                                                                                               |
| [Ue] rated operational voltage | 100...240 V AC +/- 10 % at 50/60 Hz                                                                                                                                                                                                                                                                                                 |
| Power consumption in W         | 0.1 W                                                                                                                                                                                                                                                                                                                               |
| Max output power on one port   | 18 W                                                                                                                                                                                                                                                                                                                                |
| Material                       | Plastic: housing                                                                                                                                                                                                                                                                                                                    |
| Protection type                | Short-circuit<br>Surge<br>Overheating<br>Overvoltage<br>Overcurrent                                                                                                                                                                                                                                                                 |
| Number of terminals            | 2 screw terminals                                                                                                                                                                                                                                                                                                                   |
| Shape of screw head            | Pozidriv No 1                                                                                                                                                                                                                                                                                                                       |
| Clamping connection capacity   | 2 x 0.75...2 x 2.5 mm <sup>2</sup> for rigid cable(s)<br>2 x 0.75...2 x 2.5 mm <sup>2</sup> for flexible cable(s)                                                                                                                                                                                                                   |
| Wire stripping length          | 7 mm                                                                                                                                                                                                                                                                                                                                |
| Fixing mode                    | By screws                                                                                                                                                                                                                                                                                                                           |
| Height                         | 71 mm                                                                                                                                                                                                                                                                                                                               |
| Width                          | 71 mm                                                                                                                                                                                                                                                                                                                               |
| Depth                          | 42 mm                                                                                                                                                                                                                                                                                                                               |
| Resistance to chemical agents  | Resistant to alcohol (70 %)<br>Resistant to alcohol (96 %)<br>Resistant to A-Lactic Acid<br>Resistant to diluted quaternary ammonium<br>Resistant to diluted bleach<br>Resistant to diluted ammonia<br>Resistant to soapy water<br>Resistant to crystal cleaner<br>Resistant to hydrogen peroxide 10 volumes<br>Resistant to hexane |

### Environment

|                                       |           |
|---------------------------------------|-----------|
| Ambient air temperature for operation | 0...40 °C |
| Product certifications                | EAC       |
| Electrical insulation class           | Class II  |
| IK degree of protection               | IK04      |
| IP degree of protection               | IP20      |

Offer Sustainability

|                            |                                                                                                                          |
|----------------------------|--------------------------------------------------------------------------------------------------------------------------|
| REACH Regulation           |  <a href="#">REACH Declaration</a>      |
| EU RoHS Directive          | Compliant with Exemptions                                                                                                |
| Sustainable packaging      | Yes                                                                                                                      |
| China RoHS Regulation      |  <a href="#">China RoHS Declaration</a> |
| RoHS exemption information |  <a href="#">Yes</a>                    |