

Endress+Hauser Thermometer TM311-AAC0BG2BAB4A2

Compact Pt100 temperature sensor with IO-Link and 4 to 20 mA for general and sterile applications



Picture for reference only. Product appearance may vary based on configuration

The iTHERM CompactLine TM311 is a thermometer that provides accurate and fast process temperature measurements in hygienic and aseptic applications. It is available with a common Pt100 RTD or a Pt100 RTD with TipSens technology reaching response times as low as 1.5 s (t90) for optimum process control. The sensor is very accurate even with short immersion lengths.

- Version with iTHERM TipSens offers best-in-class response times with a T90 time of 1.5 seconds
- Version with iTHERM TipSens ensures a highly accurate measurement for short immersion lengths for example in small pipelines in the food and beverages industry
- Fast installation and easy commissioning thanks to compact dimensions for installation in tight spaces
- 4...20mA and IO-Link in one device. Perfect to save costs for stock

Configuration of TM311-AAC0BG2BAB4A2:

Approval:	AA	Non-hazardous area
Output:	C	IO-Link/4-20mA, 0...+150oC
Design; Diameter Insert:	0	W/o thermowell, direct contact; 6mm
Material Wetted Parts:	B	316L
Process Connection:	G2	G1/4 male thread ISO 228, 316L
Surface Wetted Parts:	B	Ra<=0.76um/30uinch
Sensor Type; Measuring Range:	A	Pt100 TF, basic; -50...+150oC
Immersion Length U:	B4	30 mm
Thermowell Connection:	A	Not needed, no thermowell, direct contact
Neck Length E:	2	50 mm (1.97")

Alternative part number: TM311-66U0/0