

FEATURES

- Extremely high chemical resistance
- Hot water resistant
- High temperature performance a high melting point of -200 to +260°C, shortterm up to 300°C
- Excellent sliding properties with low coefficient of friction
- Non-stick surface, no materials will stick to it. PTFE is also difficult to bond or weld
- High coefficient of thermal expansion (The ratio that a material expands in accordance with changes in temperature)
- Relatively low strength and rigidity
- Excellent UV and weather resistance
- Good electrical insulation properties

Opaque Plastic Sheet, 600mm x 300mm x 3mm

RS Stock No.: 680-678



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From RS Pro a range of high-quality PTFE solid plastic sheets available in a range of sizes and thicknesses.

General Specifications

Form	Solid				
Colour	Opaque				
Material	PTFE				
Laminated	Yes				
Laminated Material	Acrylic; Epoxy Resin; Fine Weave Cotton; Glass Fibre				
Flammability Rating	UL 94 V-0				
Polymer Type	Copolymer				
Finish	Mirror				
Adhesive Backing	Yes				
Applications	Components that can be manufactured from this plastic include the following: Slide bearings and runners, Pump housings and parts, Valve seats, Tank linings, Roller coverings, Pipe linings, Filter housings, Etching plates, High frequency insulation, Seals				

Electrical Specifications

Specific Surface Resistance	10 ¹⁴ Ω
Specific Volume Resistance	10 ¹³ Ω.cm
Dielectric Constant	2.9
Dielectric Loss Factor	0.0017tg
Breakdown Voltage	17kV/mm
Dielectric Strength 23°C, 50% r.h.	49kV/mm



Mechanical Specifications

Length	600mm		
Width	300mm		
Thickness	3mm		
Density	2.18 to 2.21g/cm ³		
Tensile Strength	25MPa		
Hardness	55 Shore D		
Water absorption	0.3%		
Thermal Conductivity	0.17W/m.K		
Elongation	50%		
Impact Strength	12kJM ⁻²		
Modulus Of Elasticity	2800MPa		
Flexural Strength	91MPa		
Compression Strength	20MPa		
Compression Modulus	2300MPa		
Ball Indentation Hardness	165MPa		
Thermal Expansion	5x10 ⁻⁵ k ⁻¹		
Specific Heat	1.1J/(g.K)		
Specific Gravity	1.38		
Flexural Modulus	2600MPa		
Friction Coefficient	0.54		
Poisson Ratio	0.38kJM ⁻²		

Operation Environment Specifications

Maximum Operating Temperature	260°C
Melting Point	255°C
Glass Transition Temperature	-60°C
Vicat Softening Point	65°C

Approvals

Compliance/Certifications	CE / UR / cUR

Solid Plastic Sheets



PTFE

 Chemical Designation
 Colour
 Density

 PTFE (Polytetrafluorethylene)
 white opaque
 2.15 g/cm³

Mechanical properties	parameter	value	unit	norm		comment	
Tensile strength		22	MPa	ASTM D 4894	1)	(1) Tested on extruded and machined specimen (2) Tested on extruded and machined specimen (3)	
Elongation at break		220	%	ASTM D 4894	2)		
Compression strength	1% strain	5	MPa	ASTMD 695			
Shore hardness	Shore D	55		ASTM D 2240	3)		
Thermal properties	parameter	value	unit	norm		comment	
Glass transition temperature		- 20	°C	DIN 53765	1)	(1) Found in public sources. (2) Found in public sources.	
Service temperature	short term	260	°C	-	2)	Individual testing regarding	
Service temperature	long term	260	°C	-		application conditions is mandatory.	
Thermal expansion (CLTE)	23-100°C, long.	13	10 ⁻⁵ K ⁻¹	ASTMD 696			
Thermal conductivity		0.20	W/(K*m)	ASTMC 177			
Electrical properties	parameter	value	unit	norm		comment	
Specific surface resistance		10 ¹⁶	Ω	ASTMD 257	1)	(1) Without defects	
Specific volume resistance		10 ¹⁷	Ω*cm	ASTMD 257		••	
Dielectric strength	In air, 0.125mm thick	80	kV/mm	ASTMD 149	·	••	
Dielectric constant	50-109Hz	2.1		ASTMD 150		••	
Other properties	parameter	value	unit	norm		comment	
Water absorption	23°C	< 0.01	%	ASTMD 570		(1) Corresponding means no	
Flammability (UL94)	corresponding to	V0		DIN IEC 60695-11-10;	1)	 listing at UL (yellow card). The information might be 	
						taken from resin, stock shape or estimation. Individual testing regarding application conditions is mandatory.	