



tesa® 4549

Product Information



Easy unwinding uncoated cloth tape

Product Description

tesa® 4549 is a highly tear-resistant uncoated cloth tape. It is based on a 145 mesh rayon fabric backing and natural rubber adhesive.

tesa® 4549 is a very flexible and conformable tape. The low unwinding force makes it ideal for machine driven processes and a wide range of other applications.

Features:

- low unwinding forces, enhancing automatic dispensing
- good adhesion, even on rough surfaces
- adapts to uneven surfaces without creasing
- easy to write on, ideal marking tape
- very high tensile strength
- smooth and conformable
- available colours: black and white

Sustainable Aspects



For more information: <https://www.tesa.com/product-sustainability>

Application Fields

- Automatic machine sealing of buckets and tins
- Absorption of vibration in the automobile and appliance industries
- Belting of electrical components, nails, screws, etc.
- Bundling of bars, rods and cables
- Reinforcement and securing of edges
- Cable harnessing
- Book binding

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|----------------|-----------------------------|--------|
| • Backing material | uncoated cloth | • Bio-based carbon content | 69 % |
| • Type of adhesive | natural rubber | (according to DIN EN 16640) | |
| | | • Total thickness | 300 µm |

For latest information on this product please visit <http://l.tesa.com/?ip=04549>



tesa® 4549

Product Information

Properties/Performance Values

• Elongation at break	16 %	• Easy to write on	yes
• Tensile strength	90 N/cm	• Mesh	145 count per square inch
• Abrasion resistance	good	• Temperature resistance (removability from aluminum after 30 min exposure)	140 °C

Adhesion to Values

• steel	3.6 N/cm
---------	----------

Disclaimer

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.



For latest information on this product please visit <http://l.tesa.com/?ip=04549>