

M23-12P1N1280DU - Cable connector



1340694

<https://www.phoenixcontact.com/in/products/1340694>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M23, Cable connector, series: M23 PRO, straight, shielded: yes, Screw locking mechanism, No. of pos.: 12, Direction of rotation: Standard, contact connection type: Pin, Solder connection, cable diameter range: 3 mm ... 15 mm, coding: N, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Solutions with cross-manufacturer compatibility for standard and fast locking systems
- Modern, consistent design for highly convenient operation
- All housing can be fitted with pin or socket contacts
- Safe use in the field, thanks to high degree of protection

Commercial data

Item number	1340694
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRABA
GTIN	4063151647759
Weight per piece (including packing)	122.7 g
Weight per piece (excluding packing)	122.7 g
Customs tariff number	85366990
Country of origin	DE

M23-12P1N1280DU - Cable connector



1340694

<https://www.phoenixcontact.com/in/products/1340694>

Technical data

Notes

Notes on operation	Please observe the derating curve.
Safety note	
Safety note	WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property. • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. • The products are suitable for applications in plant, controller, and electrical device engineering. • When operating the connectors in outdoor applications, they must be separately protected against environmental influences. • Assembled products may not be manipulated or improperly opened. • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products). • When using the product in direct connection with third-party manufacturers, the user is responsible. • For operating voltages > 50 V AC, conductive connector housings must be grounded • Ensure that the protective or functional ground has been properly connected. • VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector • Only use tools recommended by Phoenix Contact • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product. • Operate the connector only when it is fully plugged in and interlocked. • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards. • Observe the minimum bending radius of the cable. Lay the cable without twisting it. • The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting

M23-12P1N1280DU - Cable connector



1340694

<https://www.phoenixcontact.com/in/products/1340694>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

Product properties

Product type	Circular connector (cable-side)
--------------	---------------------------------

Connector

Insulating body

Coding	N
Insulation body material	PA 6.6
Contact material	CuZn
Contact surface material	Ni/Au
Insertion/withdrawal cycles	100
Connection method	Solder connection
Contact switching type	Pin
Application	Signal
Number of positions	12
Direction of rotation	Standard
Connection profile	12
Contact diameter	1 mm
Signal contacts	
Litz wire cross-section	Signal contacts min. 0.08 mm ²
Litz wire cross-section	Signal contacts max. 1 mm ²
Nominal current per signal contact	8 A
Note	for max. connection cross section
Rated voltage	Signal contact 150 V
Rated surge voltage	2.5 kV
Overvoltage category	III
Degree of pollution	3
Installation height	2000 m

Housing

Housing material	GD-Zn
Type of locking	Screw locking mechanism
Pg screw connection	none
Degree of protection (plugged in)	IP66 / IP68 (2m / 24h) / IP69K
Thread type	M23

Seal

External cable diameter	3 mm ... 15 mm (Universal gasket)
Seal material	FKM

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (see to derating)
---------------------------------	-------------------------------------

M23-12P1N1280DU - Cable connector



1340694

<https://www.phoenixcontact.com/in/products/1340694>

Permanent temperature	125 °C (DIN EN 60512-9-2 / 1000 h)
-----------------------	------------------------------------

M23-12P1N1280DU - Cable connector



1340694

<https://www.phoenixcontact.com/in/products/1340694>

Drawings

Dimensional drawing



Dimensional drawing, housing


M23-12P1N1280DU - Cable connector

1340694

<https://www.phoenixcontact.com/in/products/1340694>



Schematic diagram



Contact chamber numbering (view of plug-in side), standard pin

M23-12P1N1280DU - Cable connector



1340694

<https://www.phoenixcontact.com/in/products/1340694>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1340694>

cUL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	150 V	5 A	- 18	-

UL Recognized Approval ID: E335019-20141210				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	150 V	6 A	- 18	-

cULus Recognized				
------------------	--	--	--	--

M23-12P1N1280DU - Cable connector



1340694

<https://www.phoenixcontact.com/in/products/1340694>

Classifications

ECLASS

ECLASS-11.0	27440102
ECLASS-12.0	27440116
ECLASS-13.0	27440116

ETIM

ETIM 9.0	EC002635
----------	----------

M23-12P1N1280DU - Cable connector



1340694

<https://www.phoenixcontact.com/in/products/1340694>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

M23-12P1N1280DU - Cable connector

1340694

<https://www.phoenixcontact.com/in/products/1340694>



Accessories

SF-Z0028 - Torque screwdriver

1607456

<https://www.phoenixcontact.com/in/products/1607456>

Torque screwdriver, series: RC, UC, SH, SF



SF-Z0027 - Hook wrench

1607455

<https://www.phoenixcontact.com/in/products/1607455>

Hook wrench, series: RC, UC, RF, SF



M23-12P1N1280DU - Cable connector

1340694

<https://www.phoenixcontact.com/in/products/1340694>



RF-Z0007 - Special wrench

1614347

<https://www.phoenixcontact.com/in/products/1614347>

Special wrench, series: RF



PROT-M23PRO-OT-IP20 - Plastic protective cap

1055753

<https://www.phoenixcontact.com/in/products/1055753>

Plastic protective cap, M23, series: M23 PRO



M23-12P1N1280DU - Cable connector

1340694

<https://www.phoenixcontact.com/in/products/1340694>



PROT-M23PRO-OT-IP67 - Plastic protective cap

1055749

<https://www.phoenixcontact.com/in/products/1055749>

Plastic protective cap, M23, series: M23 PRO Signal



Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

info@phoenixcontact.co.in