



HelaTape Power - Self-amalgamating Tapes

HelaTape Power 650 - Low Voltage Mastic Tape

Features and Benefits

- Self-amalgamating, low voltage insulating compound
- For quick, void-free insulation layering
- Easily moulded by hand to conform to irregular shapes
- Perfect adhesion to metal, all types of cable insulations and jackets
- Excellent thermal stability
- Provides excellent moisture seal
- Resistant to salt water, oil and corrosive chemicals
- Recommended use in conjunction with HelaTape Flex for outer jacketing



HelaTape Power 650 consists of a very thick, self-amalgamating insulating compound.

MATERIAL	Isobutene-Isoprene-Rubber (butyl rubber) (IIR)
Operating Temperature	+90 °C
Intermittent Operating Temperature	130 °C
Water Absorption	0.1 %
Elongation at break	1000 %
Volume Resistance	10 ¹⁴ Ω cm
Dielectric Strength	19.7 kV/mm



TYPE	Thickness (T)	Width (W)	Length (L)	Colour	Article-No.
HTAPE-POWER650	3.20	38.0	1.5 m	Black (BK)	711-00300

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content.