



Brand of NTN corporation

Technical data



629EEC3

Single row deep groove ball bearings



Deep groove ball bearing, radial contact, pressed steel cage, contact seals on both sides

VISUAL (S)



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	9 mm
D - External diameter	26 mm
B - Bearing/Inner ring width	8 mm
d1 - External diameter inner ring	13,9 mm
D1 - Inner diameter outer ring	22,5 mm
rs - Min fillet radius	0,3 mm
Radial clearance class	C3
Mass	0,019 kg

PRODUCT PERFORMANCE

C - Dynamic load	4800000 mN
C0 - Static load	1970000 mN
Cu - Fatigue limit load	90000 mN
f0 - Coefficient	12.4
N lim - Mechanical Limit Speed	126000 °/s
Tmin - Min operating temperature	253,15 °K
Tmax - Max operating temperature	393,15 °K

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	2.574 Hz
BPFI - Over rolling frequency on inner (60 rpm)	4.426 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	3.515 Hz
BRF - Rotational frequency - rolling element (60 rpm)	1.758 Hz
FTF - Rotational frequency - cage (60 rpm)	0.368 Hz



ABUTMENT

da min - Min shoulder diameter IR	11 mm
da max - Max shoulder diameter IR	13,9 mm
Da max - Max shoulder diameter OR	24 mm
ra max - Max shaft & housing fillet radius	0,3 mm

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$\frac{f_0 F_a}{C_0}$	e	Fa / Fr ≤ e		Fa / Fr > e	
		X	Y	X	Y
0.172	0.19	1	0	0.56	2.3
0.345	0.22				1.99
0.689	0.26				1.71
1.03	0.28				1.55
1.38	0.3				1.45
2.07	0.34				1.31
3.45	0.38				1.15
5.17	0.42				1.04
6.89	0.44				1

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
0.6	0.5

For single or DT bearing arrangement :

If $P_0 < F_r$, then use $P_0 = F_r$

