

# Parker Product Datasheet



Parker Legris PFA tubing offers 10 times greater durability than other fluoropolymer tubings under severe chemical and mechanical conditions. This tubing range is available in three material grades, offering perfect compatibility with all applications.

**PART NUMBER:** 1010T08A01  
**COLOR:** BLACK  
**TUBE I.D. (MM):** 6  
**TUBING MATERIAL:** ANTISTATIC PFA TUBING  
**TUBE O.D. (MM):** 8  
**LENGTH (M):** 10

## PRODUCT OVERVIEW

Parker Legris PFA tubing offers 10 times greater durability than other fluoropolymer tubings under severe chemical and mechanical conditions. This tubing range is available in three material grades, offering perfect compatibility with all applications.

Features/Benefits:

- Great Versatility

- Exceptional chemical inertia

- A flexible alternative to stainless steel tubing
- Broad range of working temperatures, from cryogenic to extreme heat
- Non-stick properties allowing conveyance of many fluids & gases
- Outstanding resistance to ageing
- Fluoropolymer with the lowest permeability
- Non-flammable
- UV-transparent
- Tube marking on request
- Silicone-free

#### - Three Material Grades

- Clear PFA: to cover all applications, including those requiring maximum mechanical resistance
- Colored PFA: for circuit identification
- Black Antistatic PFA: eliminates all risk of electrostatic discharge

#### Markets:

- Food and Beverage
- Power Generation Equipment
- Aircraft
- Pharmaceutical
- Medical
- Oil and Gas

## Applications:

- Applications Subjected to Severe Mechanical and Chemical Conditions
- Medical Fluids Conveying
- Gas and Compressed Air Conveying
- Applications Requiring Very Low and High Temperature
- Fire Hazard Zones
- Applications Subjected to Intensive Cleaning
- Suitable for Fuel Cells and Clean Rooms
- Thermal Management

## Technologies:

- Fluoropolymer Tubing
- PFA Tubing
- Perfluoro alkoxy Tubing
- Anti Static Tubing
- Industrial Tubing

# TECH SPECIFICATIONS

## MINIMUM OPERATING TEMPERATURE

-40 °C

## SPECIFICATIONS MET

FDA 21 CFR 177.1550 (clear)

## SPECIFICATIONS MET

UL 94 V-0 (Fire Resistance, Industrial)

|                                      |                                                             |
|--------------------------------------|-------------------------------------------------------------|
| <b>DIVISION</b>                      | Low Pressure Connectors Europe Division                     |
| <b>MAXIMUM OPERATING PRESSURE</b>    | 33 bar                                                      |
| <b>APPLICATION</b>                   | Food Processing                                             |
| <b>MEDIA</b>                         | Industrial Gases                                            |
| <b>SPECIFICATIONS MET</b>            | USP Class VI (A). Medical: External Communication Devices   |
| <b>MEDIA</b>                         | Food & Beverage                                             |
| <b>MEDIA</b>                         | Compressed Air                                              |
| <b>WEIGHT</b>                        | 0.485 kg/package                                            |
| <b>SPECIFICATIONS MET</b>            | ATEX 94/9/EC (black tubing, industrial)                     |
| <b>VACUUM PRESSURE RATING</b>        | 755 mm-Hg                                                   |
| <b>SPECIFICATIONS MET</b>            | REACH 1907/2006 (Industrial)                                |
| <b>APPLICATION</b>                   | Medical                                                     |
| <b>SPECIFICATIONS MET</b>            | PED 97/23/EC (Industrial)                                   |
| <b>APPLICATION</b>                   | Oil & Gas                                                   |
| <b>APPLICATION</b>                   | Chemicals                                                   |
| <b>APPLICATION</b>                   | Pharmaceutical                                              |
| <b>MAXIMUM OPERATING TEMPERATURE</b> | 150 °C See the Graph “Working Pressure/Working Temperature” |
| <b>SPECIFICATIONS MET</b>            | RoHS 2002/95/EC, 2011/65/EC (Industrial)                    |
| <b>APPLICATION</b>                   | Aircraft                                                    |
| <b>APPLICATION</b>                   | Clean Rooms                                                 |
| <b>MEDIA</b>                         | Medical Fluids                                              |