Product datasheet

Specifications



auxiliary contact - 1 NO + 1 NC - for P25M - 415 V - 2.2 A

Local distributor code:

22395052 21117

EAN Code: 3303430211174

Main

range of product	Acti9
Product or component type	OC contact
Device short name	NO and NC
Signal contacts composition	1 NO + 1 NC
9 mm pitches	1
Standards	EN/IEC 60947-5-1
Product certifications	SEMKO NEMKO FIMKO DEMKO CEBEC

Complementary

Range compatibility	Acti9 P25M
mounting mode	Fixed
Mounting support	DIN rail
Height	89 mm
Width	18 mm
Depth	65 mm
Connections - terminals	Clamp terminal: 2 cable(s) 1 mm² - flexible Clamp terminal: 2 cable(s) 2.5 mm² - flexible Clamp terminal: 2 cable(s) 1 mm² - rigid

Environment

Tropicalisation	2 conforming to EN/IEC 60947-5-1
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20…60 °C
Ambient air temperature for storage	-40…80 °C

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	6.6 cm
Package 1 Width	1.2 cm
Package 1 Length	9.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	43.0 g
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	9.5 cm
Package 2 Width	10.0 cm
Package 2 Length	15.0 cm
Package 2 Weight	486.0 g
Unit Type of Package 3	S03
Number of Units in Package 3	100
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	5.389 kg

Logistical informations

Country of origin	CZ

Contractual warranty

Warranty (in months)	18

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Total lifecycle Carbon footprint	**0.9 kg CO2 eq.**
Carbon footprint of the manufacturing phase [A1 to A3]	**0.3 kg CO2 eq.**
Carbon footprint of the distribution phase [A4]	**0 kg CO2 eq.**
Carbon footprint of the installation phase [A5]	**0 kg CO2 eq.**
Carbon footprint of the use phase [B2, B3, B4, B6]	**0.5 kg CO2 eq.**
Carbon footprint of the end-of-life phase [C1 to C4]	**0.1 kg CO2 eq.**
Environmental Disclosure	**Product Environmental Profile**

Use Better

Materials and Substances

Packaging made with recycled cardboard	**No**
Packaging without single use plastic	**No**
SCIP Number	**9da5f8d9-d60f-424a-bb30-a856a097686c**
EU RoHS Directive	**Compliant By Exemption**
REACh Regulation	**Reference contains Substances of Very High Concern above the threshold**
Halogen-free status	**Product contains halogen above thresholds**

Use Longer

Lifetime extension

Repair	**No**

Use Again

Repack and remanufacture

Recyclability potential, in %	**29**
End of life manual availability	**No need of specific recycling operations**
Take-back	**No**
WEEE Label	**The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**