



[All Signal Header \(245\)](#)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1725761-1
KIT, SEATING TOOL, 1X4



TE Part #1879260-2
RP 2B 2K67 0.1% 15PPM 1K RL



TE Part #3-1879514-1
CRGH1206 1% 221R 0.5W



TE Part #104809-6
07 MTE HDR SRST LATCH W/HLDWN



TE Part #1676475-1
RN 0805 9K76 0.1% 10PPM CUT LENGTH



TE Part #826938-4
4P AMPMODU II STIFT LEI



TE Part #5-338169-2
15P HDP20 PLUG ASSY



TE Part #1-928776-3
MOD2 STIFT M A-PIN



TE Part #1-1676955-6
3621D 2200UH 10%



TE Part #104809-4
05 MTE HDR SRST LATCH W/HLDWN

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1318382-6_D.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1318382-6_D.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1318382-6_D.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of 025 Receptacle Contact

Japanese

Application Specification

Japanese



Instruction Sheets

[Instruction Sheet \(non U.S.\)](#)

English

[Instruction Sheet \(non U.S.\)](#)

Japanese