



Connectors > Connector Accessories > Connector Backshells > SUPERSEAL 1.0 Connector Backshells



Connector Backshell Product Type: **Backshell**

Primary Product Material: **PA 6**

Number of Positions: **34**

Compatible With Connector Shape: **Rectangular**

Operating Temperature Range: **-40 – 125 °C [-40 – 257 °F]**

[All SUPERSEAL 1.0 Connector Backshells \(3\)](#)

Features

Product Type Features

Connector Backshell Product Type	Backshell
----------------------------------	-----------

Configuration Features

Number of Positions	34
---------------------	----

Body Features

Primary Product Color	Black
Cable Exit Angle	180°
Primary Product Material	PA 6

Housing Features

Compatible With Connector Shape	Rectangular
---------------------------------	-------------

Dimensions

Product Length	46.5 mm[1.83 in]
----------------	------------------

Usage Conditions

Operating Temperature Range	-40 – 125 °C[-40 – 257 °F]
-----------------------------	----------------------------



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | [SUPERSEAL 1.0mm](#)



Automotive Housings(22)



Automotive Seals & Cavity Plugs(1)



Automotive Terminals(10)



Rectangular Backshells & Clamps(3)

Customers Also Bought




TE Part #T2030422101-000
HDD-042-M



TE Part #254977-E
STVCD 128 F ABCD VVV 7-00 TL 4,0 * 247



TE Part #374545-E
STVC 32 M AC GG 4-00 0606 * * 247 E007 1



TE Part #364918-E
STVCD 128 M ABCD VVV 4-00 0606 * * 247



TE Part #61095-1
250 FASTON REC 14-10 AWG SPBR




TE Part #152873
14-12 PIDG NYLON RT NO 8 WHITE



TE Part #170823-3
250 FASTON SLEEVE,REC., TRANSPARENT



TE Part #323173
STRATO-THERM, HR 4 1/4 NIPL



TE Part #1SNA399963R0500
HD 6/24.DH 8 clips



TE Part #504021-1
KIT,CPL RECEP,2.5MMBNT,ST

Documents

Product Drawings
BACKSHELL,CONN KIT

English

CAD Files
3D PDF

3D

Customer View Model
ENG_CVM_CVM_2389576-1_A.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2389576-1_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2389576-1_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.