



Part Number : [2169890001](#)

Product Description : Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Upright, Through Hole, Straight Tab and Clip, Dual Row, 14 Circuits, Gold Flash (Au) Plating

Series Number : 216989

Status : Active

Product Category : I/O Connectors



Documents & Resources

Drawings

- [2169890001_sd.pdf](#)
- [2169890001-PK1.pdf](#)

3D Models and Design Files

- [2169890001_stp.zip](#)

Specifications

- [2169900001-PS.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	I/O Connectors
Series	216989
Description	Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Upright, Through Hole, Straight Tab and Clip, Dual Row, 14 Circuits, Gold Flash (Au) Plating
Application	Wire-to-Board
Component Type	Receptacle
Product Name	USB
Standard	USB 2.0
Type	C
UPC	195842116856

Electrical

Current - Maximum per Contact	1.25A
Grounding to Panel	None
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V AC/DC

Physical

Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Female
Keying to Mating Part	None

Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Resin	Nylon
Mounting Style	Upright
Net Weight	1.110/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.40mm
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.025µm
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole
Waterproof / Dustproof	No

Mates With / Use With

Mates with Part(s)

Description	Part Number
USB Shielded I/O Type C Plugs	<u>105444</u>