



# Product data sheet

## Power tools for trade & industry

Cordless Rotary Hammer with SDS max

### PRO GBH 18V-36 C



Outstanding compactness and power – the GBH 18V-36C Professional cordless SDS max hammer

#### The most important data

Battery voltage	18.0 V
Impact energy	7 J
Hammer drilling diameter range in concrete	14 – 35 mm

**Part Number** 0 611 915 001

## Technical data

### Technical data

Impact energy	7 J
Impact rate at rated speed	0 – 2,900 bpm
Rated speed	0 – 500 rpm
Battery voltage	18.0 V
Weight excl. battery	5.3 kg
Tool holder	SDS max
Packaging dimensions (width x length x height)	408 x 617 x 150 mm
Impact energy nominal	7 J

### Drilling range

Opt. app. range in concrete with hammer drill bits	14 – 35 mm
Hammer drilling diameter range in concrete	14 – 35 mm

### Drilling range

Opt. app. range in concrete with hammer drill bits	14 – 35 mm
Hammer drilling diameter range in concrete	14 – 35 mm

## Noise/vibration information

### Hammer drilling in concrete

Vibration emission value ah	11.4 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>

### Chiselling in concrete

Vibration emission value ah	10.8 m/s <sup>2</sup>
Uncertainty K	1.5 m/s <sup>2</sup>



**BOSCH**


Invented for life

# Product data sheet

Power tools for trade & industry

## Advantages:

- Extremely compact – significantly more compact than any other cordless SDS max hammer on the market
- Soft start and lock-on button for permanent chiselling
- Maximum power with lightweight design – brushless hammer with top performance of 7.0 J max at 6.1 kg



You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

