

# Vishay Semiconductors

# **Small Signal Switching Diode, High Voltage**




#### **FEATURES**

- · Silicon epitaxial planar diode
- · Fast switching diode, especially suited for applications requiring high voltage capability

• Base P/N-E3 - RoHS-compliant, commercial

please see www.vishay.com/doc?99912







• Base P/N-HE3 - RoHS-compliant, AEC-Q101 qualified

#### **MECHANICAL DATA**

Case: SOD-123

Weight: approx. 10.3 mg Packaging codes/options:

18/10K per 13" reel (8 mm tape), 10K/box 08/3K per 7" reel (8 mm tape), 15K/box

PARTS TABLE					
PART ORDERING CODE		INTERNAL CONSTRUCTION	TYPE MARKING	REMARKS	
GSD2004W	GSD2004W-E3-08 or GSD2004W-E3-18	Single diode	B6	Tape and reel	
	GSD2004W-HE3-08 or GSD2004W-HE3-18	Sirigle diode	ВО		

<b>ABSOLUTE MAXIMUM RATINGS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Continuous reverse voltage		V <sub>R</sub>	240	V	
Repetitive peak reverse voltage		$V_{RRM}$	300	V	
Forward current (continuous)		I <sub>F</sub>	225	mA	
Repetitive peak forward current		I <sub>FRM</sub>	625	mA	
Non-repetitive peak forward current	t <sub>p</sub> = 1 μs	I <sub>FSM</sub>	4	Α	
Non-repetitive peak forward current	t <sub>p</sub> = 1 s	I <sub>FSM</sub>	1	Α	
Power dissipation (1)		P <sub>tot</sub>	350	mW	

THERMAL CHARACTERISTICS (T <sub>amb</sub> = 25 °C, unless otherwise specified)					
PARAMETER	TEST CONDITION	SYMBOL	VALUE	UNIT	
Typical thermal resistance junction to ambient air (1)		R <sub>thJA</sub>	357	K/W	
Junction temperature		Tj	150	°C	
Storage temperature range		T <sub>stg</sub>	- 65 to + 150	°C	
Operating temperature range		Top	- 55 to + 150	°C	

<sup>(1)</sup> Valid provided that electrodes are kept at ambient temperature.





### www.vishay.com

# Vishay Semiconductors


<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>amb</sub> = 25 °C, unless otherwise specified)						
PARAMETER	TEST CONDITION	SYMBOL	MIN.	TYP.	MAX.	UNIT
Reverse breakdown voltage	I <sub>R</sub> = 100 μA	V <sub>(BR)</sub>	300			V
Lookaga aurront	V <sub>R</sub> = 240 V	I <sub>R</sub>			100	nA
Leakage current	$V_R = 240 \text{ V}, T_j = 150 ^{\circ}\text{C}$	I <sub>R</sub>			100	μA
Commend valtage	I <sub>F</sub> = 20 mA	V <sub>F</sub>		0.83	0.87	V
Forward voltage	I <sub>F</sub> = 100 mA	V <sub>F</sub>			1	V
Diode capacitance	$V_F = V_R = 0$ , $f = 1$ MHz	C <sub>D</sub>			5	pF
Reverse recovery time	$I_F = I_R = 30$ mA, $i_R = 3$ mA, $R_L = 100 \Omega$	t <sub>rr</sub>			50	ns


### PACKAGE DIMENSIONS in millimeters (inches): SOD-123





Mounting Pad Layout





Rev. 4 - Date: 24. Sep. 2009 Document no.: S8-V-3910.01-001 (4)



## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# **Material Category Policy**

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.

Revision: 02-Oct-12 Document Number: 91000