

## **B0677E - Marathon S3 ESD SRC**

**Collection:** Record

**Upper:** Water Resistant Technical Textile

**Lining:** SmellStop Antiodor and Antibacterial\*

**Midsole:** Fresh'n Flex

**Toecap:** SlimCap

**Sole:** Antifatigue AirTech + Tpu-Skin

**Outer Carton:** 10

### **Record**

Record antifatigue footwear collection offers an answer to the demand for lightweight design.

### **Foot Protection**

Innovation, design, styling and quality components define the Portwest foot protection collection.



### **Standards**

UNI EN ISO 20345:2012 S3 (ESD SRC)

CEI EN 61340-5-1

CEI EN 61340-4-3

CEI EN 61340-4-5

### **Features**

- Water resistant upper to prevent water penetration
- Orthopaedic made to measure footbed, complying with european norms DGUV112-191
- Electronic devices protection from electrostatic discharges
- 200 joules resistant toe-cap
- Puncture resistant sole
- Shock absorption in the heel region
- Hydrocarbons resistant
- Anti-static footwear
- Non-magnetic - nickel and ferrous free
- Men's width
- Women's width

**B0677E - Marathon S3 ESD SRC**  
**Commodity Code: 6404199000**

**Test House**

A.N.C.I. Servizi S.R.L (CIMAC) (Notified Body No.: NB: 0465)

Via Alberto Riva Villasanta, 3  
, Italy

Cert No: F-113-02436-19 Rev.1

**Carton Dimensions/Weight**

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m <sup>3</sup> )	EAN13	GTIN/DUN14
B0677EBKB36		67.0	41.0	36.0	1.0080	0.0989	8050262500871	
B0677EBKB37		67.0	41.0	36.0	1.0460	0.0989	8050262500888	
B0677EBKB38		67.0	41.0	36.0	1.0620	0.0989	8050262500895	
B0677EBKB39		67.0	41.0	36.0	1.1060	0.0989	8050262500901	
B0677EBKB40		67.0	41.0	36.0	1.1500	0.0989	8050262500918	
B0677EBKB41		67.0	41.0	36.0	1.2000	0.0989	8050262500925	
B0677EBKB42		67.0	41.0	36.0	1.2280	0.0989	8050262500932	
B0677EBKB43		67.0	41.0	36.0	1.2500	0.0989	8050262500949	
B0677EBKB44		67.0	41.0	36.0	1.2840	0.0989	8050262500956	
B0677EBKB45		67.0	41.0	36.0	1.3340	0.0989	8050262500963	
B0677EBKB46		67.0	41.0	36.0	1.3680	0.0989	8050262500970	
B0677EBKB47		67.0	41.0	36.0	1.4400	0.0989	8050262500987	
B0677EBKB48		67.0	41.0	36.0	1.5100	0.0989	8050262500994	