

54V XR FLEXVOLT 52MM SDS-MAX HAMMER DRILL - BARE UNIT

DCH773N



True corded performance

An anti rotation system detects a loss of tool control, and reacts by instantly cutting the power

Active vibration control system incorporating a floating rear handle and damped side handle to reduce vibration

OVERVIEW

SPECIFICATIONS

SPECIFICATIONS

Tool Holder	SDS-Max
Battery chemistry	Li-Ion
Impact energy (EPTA 05/2009)	19.4 J
Max. Drilling Capacity [Concrete]	52 mm
Max. Drilling Capacity [Core bit]	150 mm
Weight	9.4 kg
Length	284 mm
Height	644 mm
Width	115 mm
Hand/Arm Vibration - Hammer drilling into concrete	10.1 m/s ²
Uncertainty K 1 (Vibration)	1.5 m/s ²
Hand/Arm Vibration - Chiselling	

✕ Cancel

✓ Capture