

M18 FHAFOH16-302X

M18 FUEL™ 16 MM SDS-PLUS HAMMER WITH INTEGRATED DUST EXTRACTOR

World's first integrated dust extractor drilling hammer

The highly efficient HEPA filter collects 99.97% of airborne particles down to 0.3 microns

AUTOSTOP™ shuts down the tool to protect the user of sharp movement in bind up situations

Optimised for overhead applications

AUTOPULSE™ on-board automatic filter cleaning mechanism for an on-tool dust extractor, which increases the air flow efficiency as well as the filter life time

Anti-vibration system (AVS) for decreased user fatigue and lower vibration exposure. Also, an added anti-vibration side handle for lowering the vibration exposure even further

Translucent dust box allows user to see the current level of dust inside as well as when the dust box is full

ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality

The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability

Flexible dust shroud increasing the user's comfort and efficiency, especially when drilling overhead between pipes and tight spaces

Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Max. percussion rate (bpm)	4,740
Max. drilling concrete (mm)	16
Weight with battery pack (EPTA) (kg)	3.3 (M18 HB3)
Kit included	2 x M18 HB3 Battery packs, M12-18 FC Charger, HD Box
Article number	4933493533