




Passive Components > Resistors > Surface Mount Resistors



Resistance Value: **.01 Ω**
Resistor Type: **Low Ohmic Resistor**
Element Type: **Foil**
Power Rating: **1 W**
Resistance Class: **Up to 1k Ω**

Features

Product Type Features

Resistor Type	Low Ohmic Resistor
Element Type	Foil

Configuration Features

Number of Resistors	1
---------------------	---

Electrical Characteristics

Resistance Value	.01 Ω
Power Rating	1 W
Resistance Class	Up to 1k Ω
Passive Component Tolerance	5 %

Termination Features

Surface Mount Resistor Termination Type	Solder
Number of Terminations	2

Usage Conditions

Temperature Coefficient	± 100 ppm/ $^{\circ}\text{C}$
-------------------------	-----------------------------------

Packaging Features

Packaging Method	Loose Piece - Bag
------------------	-------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | CGS SMD



High Speed Backplane Connectors(1)




Surface Mount Resistors(34)


Customers Also Bought



TE Part #2102157-2
Fortis Zd 3Pr 10Col Vert Full Shrd Assy




TE Part #CAT-ZD-BPC-HEADER
Backplane Connector: Plug-in module




TE Part #1-1879266-1
RP 2B 332K 0.1% 15PPM 1K RL




TE Part #2102079-2
Pin assy, 60 psn, lead free, Mezalok



TE Part #6-1437166-1
FSP-22A-20



TE Part #7-2180760-3
STRADA MESA,HD,HF,024,000,06,SN,Y,23



TE Part #1879267-2
RP 2B 681K 0.1% 15PPM 1K RL



TE Part #1623946-1
SC10-10-0515-10 1.5UH AMMO 1000



TE Part #826655-9
9P AMPMODU II STIFT LEI

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1624253-1_BA.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1624253-1_BA.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1624253-1_BA.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1309350_PASSIVE_COMPONENT

English

8-1773459-4_POWER_FILTERING_AND_RESISTIVE_SOLUTIONS_FOR_ELEVATORS_AND_ESCALATORS

English



SMD Precision Current Sense Resistor - Type S Series - Tyco Electronics Passives

English