



Connectors > Rectangular Connectors > Rectangular Connector Hoods & Bases



Hood & Base Connector Product Type: **Hood**

Cable Entry Location: **Bottom**

Hood & Base Locking Device Type: **Side Clip**

Features

Product Type Features

|                                    |      |
|------------------------------------|------|
| Hood & Base Connector Product Type | Hood |
|------------------------------------|------|

Body Features

|                       |        |
|-----------------------|--------|
| Primary Product Color | Gray   |
| Cable Entry Location  | Bottom |

Mechanical Attachment

|                                 |                |
|---------------------------------|----------------|
| Thread Size                     | PG16           |
| Locking Device Location         | Housing Bottom |
| Hood & Base Locking Device Type | Side Clip      |

Housing Features

|                  |          |
|------------------|----------|
| Housing Material | Aluminum |
|------------------|----------|

Dimensions

|                |                 |
|----------------|-----------------|
| Product Width  | 78 mm[3.07 in]  |
| Product Length | 60 mm[2.36 in]  |
| Product Height | 53.5 mm[2.1 in] |

Usage Conditions

|                     |     |
|---------------------|-----|
| Corrosion Protected | Yes |
|---------------------|-----|

Packaging Features

|                    |        |
|--------------------|--------|
| Packaging Method   | Carton |
| Packaging Quantity | 5      |



Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                                                         |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant with Exemptions                                                                                                               |
| EU ELV Directive 2000/53/EC                   | Compliant with Exemptions                                                                                                               |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold                                                                                                    |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JUN 2018 (191)<br>SVHC > Threshold:<br>Not Yet Reviewed |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                          |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                            |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | HDC IP65



Connector Caps & Covers(25)



Rectangular Connector Hoods & Bases (1232)

Customers Also Bought



TE Part #T2120100219-000  
ZGG-10DSTK,1-7,2-8,3-9,4-6,5-10



TE Part #1SNA195638R2300  
M4/6.4A.P



TE Part #T2106062201-000  
HWK6/6-012-F



TE Part #T1730060000-000  
H6B-TBF-T



TE Part #1-480711-9  
15P UMNLCAP HSG BLK



TE Part #T2020082201-000  
HD-008-F




TE Part #640250-1  
01P SL156 HSG W/LCK RAMP NATL



TE Part #T2120100220-000  
ZGGP-H10BSK 1-7/2-8/3-9/4-6/5-10



TE Part #T0931003003-000  
CODING-PIN-M3



TE Part #1473203-1  
025 CAP ASSY 16P P/BACK BRCKT