

r

## Features

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- A wide range of lubricants are available to meet specific requirements within a temperature range of -60°C to 200°C.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.

## RS PRO Oilite® Plain Bearing

RS Stock No.: 0528300



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

RS PRO is offering range of Oilite® plain bearings - self-lubricating bearings that are made from metal alloys with pores that channel lubricants between the bearing itself and the shaft.

- Standard Oilite® bearings are impregnated with highly refined mineral oil to ISO VG (SAE 30) having a high viscosity index and containing anti-oxidant, anti-rust and defoamant additives.
- Lubricant : Shell Tellus S2 MX68
- Temperature range of -15°C to +75°C.
- Standard Oilite® oil retaining tin bronze is the generally specified material. It gives a good balance between strength, wear resistance, conformability, and durability in operation. Ideal in a wide variety of applications where self-lubricating properties are required over a long period of time.
- All dimensions and tolerances of our metric ranges conform to ISO 2795:1991
- Wide range of metric and imperial sizes
- Wide range of different types: Plain, Flanged

\* Below dimensions in mm



## Specifications

### Details

Inner Diameter	12	Outer Diameter	18	Length	16
Tolerance Range	UK Standard				

### Material Specification

Structure	Oil impregnated sintered bronze*		
Max PV (N/mm² x m/s)	1.8	Max Static load (N/mm²)	50
Max Dynamic load (N/mm²)	14	Max Sliding speed (m/s)	5
Operating temperature (°C)	-60 to 200* *dependant on lubrication	Density (g/cm³)	6.6
Radial crushing strength (K Min M/mm²)	160		

### Tolerances & Fittings (Metric)

	Min	Max	Tolerance
Inside Diameter	12.006	12.024	G7
Outside Diameter	18.028	18.046	s7
Overall Length	15.865	16.135	js13
Recommended Housing Size	18.000	18.018	H7
Shaft Diameter	11.966	11.984	f7
Fitting Pin Size	12.007	12.015	m5
Concentricity Max	0.043	0.043	IT9
Inside Diameter When Fitted	12.000	12.018	H7

