

# Servo motor EMMT-AS-100-L-HS-RMY

Part number: 8160658

**FESTO**



 [General operating condition](#)

## Data sheet

| Feature                                                   | Value                                                                            |
|-----------------------------------------------------------|----------------------------------------------------------------------------------|
| Ambient temperature                                       | -40 °C ... 40 °C                                                                 |
| Note on ambient temperature                               | Up to 80°C with derating of -1.75% per degree Celsius                            |
| Max. installation height                                  | 4000 m                                                                           |
| Note on max. installation height                          | As of 1,000 m: only with derating of -1.0% per 100 m                             |
| Storage temperature                                       | -40 °C ... 70 °C                                                                 |
| Relative air humidity                                     | 0 - 90%                                                                          |
| Conforms to standard                                      | IEC 60034                                                                        |
| Temperature class as per EN 60034-1                       | F                                                                                |
| Max. winding temperature                                  | 155 °C                                                                           |
| Rating class as per EN 60034-1                            | S1                                                                               |
| Temperature monitoring                                    | Digital motor temperature transmission via EnDat® 2.2                            |
| Motor type to EN 60034-7                                  | IM V1<br>IM V3                                                                   |
| Mounting position                                         | Any                                                                              |
| Degree of protection                                      | IP40                                                                             |
| Note on degree of protection                              | IP67 for motor housing including connection components                           |
| Concentricity, coaxiality, axial runout to DIN SPEC 42955 | N                                                                                |
| Balance quality                                           | G 2.5                                                                            |
| Detent torque                                             | <1.0% of peak torque                                                             |
| Bearing lifetime under nominal conditions                 | 20000 h                                                                          |
| Interface code, motor out                                 | 100A                                                                             |
| Electrical connection 1, connection type                  | Hybrid plug                                                                      |
| Electrical connection 1, connector system                 | M23x1                                                                            |
| Electrical connection 1, number of connections/cores      | 15                                                                               |
| Electrical connection 1, connection pattern               | 00995913                                                                         |
| Pollution degree                                          | 2                                                                                |
| Note on materials                                         | RoHS compliant                                                                   |
| Corrosion resistance class CRC                            | 0 - No corrosion stress                                                          |
| LABS (PWIS) conformity                                    | VDMA24364 zone III                                                               |
| Vibration resistance                                      | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6 |
| Shock resistance                                          | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27                |
| Approval                                                  | RCM<br>German Technical Control Board (TÜV)<br>c UL us - Recognised (Oil)        |

| Feature                                                     | Value                                                                                                                       |
|-------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| CE mark (see declaration of conformity)                     | To EU EMC Directive<br>To EU Low Voltage Directive<br>In accordance with EU RoHS Directive                                  |
| UKCA marking (see declaration of conformity)                | To UK RoHS instructions<br>To UK regulations for electrical equipment                                                       |
| Certificate issuing authority                               | TÜV 968/INS 464.00/24<br>UL E342973                                                                                         |
| Nominal operating voltage DC                                | 680 V                                                                                                                       |
| Type of winding switch                                      | Star inside                                                                                                                 |
| Number of pole pairs                                        | 5                                                                                                                           |
| Standstill torque                                           | 10.8 Nm                                                                                                                     |
| Nominal torque                                              | 7.2 Nm                                                                                                                      |
| Peak torque                                                 | 30.5 Nm                                                                                                                     |
| Nominal rotary speed                                        | 2700 rpm                                                                                                                    |
| Max. rotational speed                                       | 4530 rpm                                                                                                                    |
| Max. mechanical speed                                       | 13000 rpm                                                                                                                   |
| Angular acceleration                                        | $\leq 100000 \text{ rad/s}^2$                                                                                               |
| Nominal power rating of motor                               | 2030 W                                                                                                                      |
| Continuous stall current                                    | 7 A                                                                                                                         |
| Nominal motor current                                       | 4.7 A                                                                                                                       |
| Peak current                                                | 28.6 A                                                                                                                      |
| Motor constant                                              | 1.54 Nm/A                                                                                                                   |
| Standstill torque constant                                  | 1.75 Nm/A                                                                                                                   |
| Voltage constant, phase-to-phase                            | 106 mV/min                                                                                                                  |
| Phase-phase winding resistance                              | 1.49 Ohm                                                                                                                    |
| Phase-phase winding inductance                              | 15.7 mH                                                                                                                     |
| Winding longitudinal inductivity Ld (phase)                 | 8.7 mH                                                                                                                      |
| Winding cross inductivity Lq (phase)                        | 11.8 mH                                                                                                                     |
| Electric time constant                                      | 15.8 ms                                                                                                                     |
| Thermal time constant                                       | 71 min                                                                                                                      |
| Thermal resistance                                          | 0.46 K/W                                                                                                                    |
| Measuring flange                                            | 300 x 300 x 20 mm, steel                                                                                                    |
| Total mass moment of inertia of output                      | 5.77 kgcm <sup>2</sup>                                                                                                      |
| Product weight                                              | 8700 g                                                                                                                      |
| Permissible axial shaft load                                | 200 N                                                                                                                       |
| Permissible radial shaft load                               | 1110 N                                                                                                                      |
| Rotor position sensor                                       | Absolute multi-turn safety encoder                                                                                          |
| rotor position sensor, manufacturer designation             | EQI 1331                                                                                                                    |
| rotor position sensor, absolute detectable revolutions      | 4096                                                                                                                        |
| Rotor position encoder interface                            | EnDat 22                                                                                                                    |
| Rotor position sensor, encoder measuring principle          | Inductive                                                                                                                   |
| rotor position sensor, DC operating voltage                 | 5 V                                                                                                                         |
| rotor position sensor, DC operating voltage range           | 3.6 V ... 14 V                                                                                                              |
| rotor position sensor, position values per revolution       | 524288                                                                                                                      |
| Rotor position transducer resolution                        | 19 bit                                                                                                                      |
| rotor position sensor, system accuracy of angle measurement | -65 arcsec ... 65 arcsec                                                                                                    |
| Safety device                                               | Safety device                                                                                                               |
| Maximum SIL                                                 | Safety integrity level 3<br>See user documentation                                                                          |
| Safety sub-functions up to SIL2                             | Reliable recording and transmission of single-turn position data                                                            |
| Safety sub-functions up to SIL3                             | Reliable recording and transmission of single-turn position data, only with additional software function in the servo drive |
| Maximum PL and category                                     | Performance Level e, category 3<br>See user documentation                                                                   |
| Safety sub-function up to PL d, Cat. 3                      | Reliable recording and transmission of single-turn position data                                                            |

| Feature                                | Value                                                                                                                       |
|----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------|
| Safety sub-function up to PL e, Cat. 3 | Reliable recording and transmission of single-turn position data, only with additional software function in the servo drive |
| PFHd, subcomponent                     | 15 x 10E-9, encoder                                                                                                         |
| Duration of use Tm, subcomponent       | 20 years, rotor position encoder                                                                                            |
| Energy efficiency                      | ENEFF (CN) / Class 2                                                                                                        |