



## Main

Range	TeSys
Product name	TeSys GK1
Product or component type	Fuse-disconnector
Device short name	GK1 E
Poles description	3P

## Complementary

Mounting support	Rail
Mounting position	Vertical +/- 23°
Control type	Toggle
[Ue] rated operational voltage	690 V for power circuit 500 V for signalling circuit 440 V for signalling circuit
[Ie] rated operational current	50 A for power circuit 6 A for signalling circuit
Contacts type and composition	2 NO early-break 1 C/O upstream device tripping on blown fuse
Fuse size	14 x 51 mm
Fuse type	AM GG
Connections - terminals	1 solid cable(s) 2.5...25 mm <sup>2</sup> on connector for power circuit 1 flexible cable(s) 2.5...25 mm <sup>2</sup> without cable end on connector for power circuit 1 flexible cable(s) 2.5...16 mm <sup>2</sup> with cable end on connector for power circuit
Tightening torque	2 N.m power circuit : on connector

## Environment

Standards	IEC 60947-3
IP degree of protection	IP20
Protective treatment	TC
Ambient air temperature for operation	-50...70 °C
Height	97 mm
Width	115 mm

---

Depth	89.5 mm
Product weight	0.51 kg

---

### Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---