




TE Internal #: T2210002010-030

Wire-to-Wire, Sealable, Signal, 22 – 24 AWG, .35 – .2 mm² Wire,
Receptacle, Socket, -40 – 85 °C [-40 – 185 °F]

[View on TE.com >](#)

Connectors > Circular Connectors > Standard Circular Connectors



Connector System: **Wire-to-Wire**

Sealable: **Yes**

Contact Current Rating (Max): **5 A**

Circuit Application: **Signal**

Hermetically Sealed: **No**

Features

Product Type Features

Connector System	Wire-to-Wire
Sealable	Yes
Circular Connector Type	Receptacle

Configuration Features

Contacts Preloaded	No
--------------------	----

Body Features

Hermetically Sealed	No
---------------------	----

Contact Features

Contact Current Rating (Max)	5 A
Circular Connector Contact Type	Socket

Mechanical Attachment

Mating Retention	With
------------------	------

Dimensions

Wire Size	22 – 24 AWG
-----------	-------------



Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
Shielded	No

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts





TE Part # CAT-G83-EPSC
[Easy-Lock Plastic Signal Connector](#)



TE Part # 2473754-2
[SINGLE WIRE SEAL](#)



TE Part # T2210001010-000
[DIA1.0 MALE STAMPING CONTACT, AU PLATED](#)

Customers Also Bought



TE Part #CAT-G83-EPSC
[Easy-Lock Plastic Signal Connector](#)



TE Part #T2210001010-001
[DIA1.0 MALE STAMPING CONTACT, TIN PLATED](#)

Documents

Product Drawings

[DIA1.0 FEMALE STAMPING CONTACT,AU PLATED](#)

English

CAD Files

Customer View Model

[ENG_CVM_CVM_T2210002010-030_A.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_CVM_T2210002010-030_A.3d_igs.zip](#)

English

3D PDF

3D

Customer View Model

[ENG_CVM_CVM_T2210002010-030_A.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Easy-Lock Plastic Signal Connectors\(PSC\)](#)

English

[Easy-Lock Plastic Signal Connectors\(PSC\)](#)

Product Specifications

[Application Specification](#)

English

T2210002010-030

Wire-to-Wire, Sealable, Signal, 22 – 24 AWG, .35 – .2 mm² Wire, Receptacle, Socket,
-40 – 85 °C [-40 – 185 °F]

