




PRODUCT INFORMATION

**tesa® 4438**

UV Surface Protection Tape



**Product Description**

The combination of the impregnated backing material with the high UV resistance facilitates multiple working processes in only one covering process.

**Main Applications**

This tape is especially suited for all renovation works, particularly for outdoor painting, facade renovation as well as for heat protection. tesa® 4438 is especially suitable for the sticking on water diluted acrylic paints. It can be used as a protection tape during transport or storage of high value surfaces. tesa® 4438 is suitable for short term masking during wave soldering and other high temperature processes as well.

**Technical Data**

Backing material	slightly-creped paper
Type of adhesive	acrylic
Total thickness	167 µm
Adhesion to steel	4 N/cm
Elongation at break	5 %
Tensile strength	33 N/cm
UV-resistance	12 Weeks

### Properties

Suitable for sensitive surfaces	++
Suitable for rough surfaces	+
Paint anchorage	++
Sharp colour Edge	+
Conformability	+
Hand tearability	++

Evaluation across relevant tesa assortment: ++ very good, + good, o medium, - low

tesa® products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, expressed or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa® product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to advise you.

#### tesa A/S

Klintehøj Vaenge 12  
3460 Birkerød

Phone: +45 (45) 998 200

Fax: +45 (45) 810 145

<http://www.tesa.dk> 

#### tesa SE

Quickbornstraße 24  
20253 Hamburg

Phone: +49 (40) 4909-101

Fax: +49 (40) 4909-6060

<http://www.tesa.de> 