

Eaton 024355

Catalog Number: 024355

Eaton xEnergy Safety Ci LV systems LV switchgear. Flange, closed, HxWxD=116x329x23mm

General specifications



Product Name	Catalog Number
Eaton xEnergy Safety Ci flange plate	024355
EAN	Product Length/Depth
4015080243557	115 mm
Product Height	Product Width
23 mm	330 mm
Product Weight	Compliances
0.284 kg	RoHS conform

Product specifications

Used with

375 mm (enclosure dimensions)

Basic enclosure

Accessory for basic enclosures

xEnergy Safety Ci

Special features

Sponge-rubber, captive
gasket

Quick mounting using
wedge-lock fasteners
(included as standard)

Type

Accessory for basic
enclosures

Basic enclosure

xEnergy Safety Ci

Accessory/spare part type

Flanges

Unit type

Modular system

Number of connector holes

0

Suitable for nominal thread (PG) - max

50

Suitable for nominal thread (PG) - min

16

Cable entry type

Drill as required

Degree of protection

Other

Surface protection

Untreated

Shape

Straight

Material

Plastic

Resources

Brochures

[eaton-xenergy-safety-ci-subway-line-success-story-en-us.pdf](#)

[eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf](#)

Catalogs

[eaton-xenergy-ci-safety-catalog-ca015006en-en-us.pdf](#)

Drawings

[eaton-enclosures-flanges-xeffect-ci-enclosure-dimensions-003.eps](#)

[eaton-enclosures-flange-xenergy-safety-ci-flange-plate-dimensions.eps](#)

Installation instructions

[IL0566](#)

mCAD model

[fl4_x.dwg](#)

[fl4_x.stp](#)

Model

Blind

Thread type

None

Thickness

4 mm

Suitable for cable diameter - max

0 mm

Suitable for cable diameter - min

0 mm



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia