




Cable Assemblies > RF Cable Assemblies



Cable Assembly Type: **OSMT to SMA**

Cable Assembly Length: **.2 m [.65 ft]**

Cable Color: **Blue**

Operating Frequency: **0 – 6 GHz**

Impedance: **50 Ω**

Features

Product Type Features

Cable Assembly Type	OSMT to SMA
Cable Assembly (End A)	OSMT Jack
Cable Assembly (End B)	SMA Plug
Coax Cable Type	9950-48

Configuration Features

Number of Connectorized Ends	2
------------------------------	---

Electrical Characteristics

Operating Voltage	250 VAC
Insulation Resistance	1000 MΩ
Impedance	50 Ω

Body Features

Conductor Material	Copper Clad Steel
Strain Relief Type	HST
Shield Plating Material	Tin
Conductor Plating Material	Tin
Shield Material	Copper Wire
Cable Color	Blue
Jacket Material	PVC

Contact Features

Ferrule Plating Material	Nickel
--------------------------	--------



Contact Mating Area Plating Material	Gold (Au)
Ferrule Material	Copper
Contact Base Material	Beryllium Copper
Center Contact Plating Material	Gold

Mechanical Attachment

Mating Diameter	2.8 mm
-----------------	--------

Dimensions

Wire Size	30 AWG
Mated Height	3.1 mm
Outside Cable Diameter	1.91 mm[.075 in]

Operation/Application

Shielded	Yes
Operating Frequency	0 – 6 GHz

Other

Dielectric Material	Polypropylene
Cable Assembly Length	.2 m[.65 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Yet Reviewed
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: DEC 2014 (161) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products



will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Customers Also Bought

Documents

Product Drawings

9950 4200 01

English

9950 4200 01

English

CAD Files

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_1064391-1_E.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1064391-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1064391-1_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1307191 RF Coax Products Catalog](#)

English