

Technical data sheet

Article number:
315-50640

TR27-6.4/3.2



Product Group	Heat shrinkable tubing 2:1 - Flame retardant
Product Family	TR27
Material	Polyolefin, cross-linked (PO-X)
Colour	Black (BK)
Behaviour at Heat Shock	not cracking, not dripping, not fluid
Dielectric Strength [Test method]	15 kV/mm [IEC 684 P2]
Elongation at break	200%
Heat Shock Test	4h/150°C
Longitudinal Change After Shrinkage	+5%/-10% max.
Min. Shrink Temperature - °C	+115 °C
Operating Temperature	-40 °C to +105 °C
Package Content packed in	metre
Pack Cont.	60 m
Recov. Ø d max.	3.2 mm
Shrink Ratio	2:1
Specifications	EN 45545-2
Supplied Ø D min.	6.4 mm
Tensile Strength	7 MPa
Wall (WT)	0.64 mm
Water Absorption	1.0 %

HF✓

LFH✓

RoHS✓

EN 45545-2