

Multi Function Power Head LXT®

DUX18

18V • 0 - 9 700 min⁻¹

Powerful cordless LXT® Multi function power head

DUX18 has a High / Low 2-speed selection and variable speed control by trigger. Multi-tool system consisting of power head and versatile optional attachments is ideal for a wide range of applications.



LXT BL MOTOR AFT

Technical specifications

Nominal Battery Voltage	18 V
Voltage LXT	✓
Brushless Motor	✓
No load speed	0 - 6800 / 9700 min ⁻¹
Sound Pressure Level (L _{pA})	70 - 95 dB(A)
Sound Power Level (L _{WA})	83,2 - 104 dB(A)
Noise Uncertainty (K Factor)	0,2 - 3,8 dB(A)
Tool weight with battery	4,0 - 10,3 kg
Product Dimensions (L x W x H):	983 x 318 x 175 mm
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Product net weight	2,4 kg
Handle Type	O

User benefits

- Variable speed control dial enables user to match the speed to the application for greater versatility
- Electric brake for maximum productivity and increased operator safety
- Brushless maintenance-free and long-life motor
- Battery protection system automatically shuts off power when the battery level is low
- Soft start for smooth start-ups

Link to product - www.makita.uk.com



Related products

Optional AC

127508-0

Band Assembly



1912V6-6

Shear Blade Assembly 330 Set



1913C9-3

Ground Trimmer Attachment Set



191D89-4

Trimmer head Tap & Go 2,0 mm, M10



191M56-3

Rotary scissor attachment, EM407MP



191N31-5

Grass trimmer attachment, 300 mm,



191P72-3

Blower attachment, UB401MP



191T38-7

Pole Saw Attachment, 300 mm, 1/4",



195638-5

Soft Carrying Bag 1200 x 330 x 300



196256-2

Split Shaft Attachment



198768-1

Brush cutter attachment set



Other

User manual

Parts drawing