

## INSTRUCTIONS FOR USE

## COMPLEX DESIGN

### MERCURY® gloves

#### A. Use

These gloves are designed to protect the hand against heavy duty mechanical applications including heat ( up to 450 °C ) and cut risks.

They are in conformity and are marked as per requirements of the European Directive 89/686/EEC and its Amendments and they are in compliance with the European Standards EN 420, EN 388 and EN 407.



EC-Type examination certificate from DuPont ( I.D. 0479 ) and EC-Quality Control for the final product by Centexbel Belgium ( I.D. 0493 ).

#### B. Precautions for use

NEVER USE THESE GLOVES AGAINST CHEMICALS. The gloves are not puncture resistant and should not be used for protection against serrated blades.

Do not use longer than 18 seconds at 250 °C. Do not use against temperatures exceeding 450 °C.

Before usage, inspect the gloves for any defects or imperfections. Avoid wearing damaged or worn out gloves.

#### C. Ingredients / Hazardous ingredients

These gloves do not contain any ingredients which are known to be a possible cause of allergies to sensitised people.

If allergic reactions would occur, obtain medical advice immediately.

#### **D. Care instructions**

Storage : Keep out from direct sunlight; store in a cool and dry place.  
Keep out from sources of ozone or ignition.

Cleaning : The gloves can be laundered at 40 °C maximum.

#### **E. Disposal**

Used gloves may be contaminated with infectious or other hazardous materials.  
Dispose of according to Local Authority Regulations. Landfill or incinerate under controlled conditions.

Ansell Ltd.  
Internationale Laan 55  
1070 Brussels  
Belgium

Type	Reference	Size	Length
Knitwrist glove	43-113	10	330 mm

## INSTRUCTIONS FOR USE


## COMPLEX DESIGN

### MERCURY® Mitten

#### A. Use

These mitten are designed to protect the hand against heavy duty mechanical applications including heat ( up to 450 °C ) and cut risks.

They are in conformity and are marked as per requirements of the European Directive 89/686/EEC and its Amendments and they are in compliance with the European Standards EN 420, EN 388 and EN 407.



EC-Type examination certificate from DuPont ( I.D. 0479 ) and EC-Quality Control for the final product by Centexbel Belgium ( I.D. 0493 ).

#### B. Precautions for use

NEVER USE THESE MITTEN AGAINST CHEMICALS. The mitten are not puncture resistant and should not be used for protection against serrated blades.

Do not use longer then 18 seconds at 250 °C. Do not use against temperatures exceeding 450 °C.

Before usage, inspect the mitten for any defects or imperfections. Avoid wearing damaged or worn out mitten.

#### C. Ingredients / Hazardous ingredients

These mitten do not contain any ingredients which are known to be a possible cause of allergies to sensitised people.

If allergic reactions would occur, obtain medical advice immediately.

#### **D. Care instructions**

Storage : Keep out from direct sunlight; store in a cool and dry place.  
Keep out from sources of ozone or ignition.

Cleaning : The mitten can be laundered at 40 °C maximum.

#### **E. Disposal**

Used mitten may be contaminated with infectious or other hazardous materials.  
Dispose of according to Local Authority Regulations. Landfill or incinerate under controlled conditions.

Ansell Protective Products  
Internationale Laan 55  
1070 Brussels  
Belgium

Type	Reference	Size	Length
Knitwrist mitten	43-213	10	330 mm